



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## B2013SS4 BLTF 2" SSRGD STR Strap

*Cooper B-Line/Cable Tray*

Catalog Number	B2013SS4
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series O.D. Pipe and Conduit Clamp, 0.1040" H X 4.3940" L X 1.25" W, Steel Material, Pipe or Conduit Clamps
Weight per unit	0.3400 (lbs/each)
Product Category	Channel & Strut Fittings

### Features

dimensions	4.3940 IN X 1.2500 IN X 0.1040 IN
Material	304 Stainless Steel

### Material, Color, and Finish

Finish	STAINLESS STEEL TYPE 304
--------	--------------------------

### Dimensions and Weight

Size	2 in
------	------

### Descriptions

Also Known As...	Strut channel Strut
Construction	TWO PIECE
Description	BLTF 2" SSRGD STR STRAP
extra long description	B-LINE B2013SS4 2"-RIGID CONDUIT CL
Features	Eaton offers a wide variety of B-Line series pipe clamps and accessories used for the support and attachment of pipe to structural members.
Long Description	Eaton B-Line series O.D. pipe and conduit clamp, 0.1040" H x 4.3940" L x 1.25" W, Steel material, Pipe or conduit clamps
Product Type	2"-Rigid Conduit Clamp, 2", SSL 304
similar brands	Unistrut
Special Features	Includes Combination Recess Hex Head Machine Screw and Square Nut

### Manufacturer Information

Brand	Eaton
GTIN	00781011610685
Manufacturers Part Number	B2013SS4
UPC	781011610685

### Taxonomies, Classifications, and Categories

Category Description	STRUT CHANNEL
Type	O.D. pipe and conduit clamp



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	50
Weight Per each	0.34

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Mounting standard	CHANNEL Not Applicable