



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

7520 Eastgate Blvd Suite 100  
37122-0000, TN Mt. Juliet  
Phone: 615-257-4146  
Fax: 615-257-4147



## B2016PAZN BLTF 3-1/2" Zinc Plate Pa Rigid Pipe Clamp

*Cooper B-Line/Cable Tray*

Catalog Number	B2016PAZN
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Pre-Assembled O.D. Pipe and Conduit Clamp, 0.0994" H X 6.1410" L X 1.25" W, Stainless Steel
Weight per unit	0.5600 (lbs/each)
Product Category	Channel & Strut Fittings

### Features

dimensions	6.1410 IN X 1.2500 IN X 0.0994 IN
Material	11 Gauge Low Carbon Steel

### Material, Color, and Finish

Finish	Zinc Plated
--------	-------------

### Dimensions and Weight

Size	3-1/2 in
------	----------

### Descriptions

Construction	TWO PIECE
Description	BLTF 3-1/2" ZINC PLATE PA RIGID PIPE CLAMP
extra long description	B-LINE B2016PAZN 3 1/2" PIPE/CONDUIT
Features	Eaton offers a wide variety of B-Line series pipe clamps and accessories used for the support and attachment of pipe to structural members.
Long Description	Eaton B-Line series pre-assembled O.D. pipe and conduit clamp, 0.0994" H x 6.1410" L x 1.25" W, Stainless steel
Product Type	3 1/2" Pipe/Conduit Clamp, Pre-Asm, Rigid, 3 1/2", ZN PLTD
Special Features	Includes Combination Recess Hex Head Machine Screw and Square Nut

### Manufacturer Information

Brand	Eaton
GTIN	00781011610944
Manufacturers Part Number	B2016PAZN
UPC	781011610944

### Taxonomies, Classifications, and Categories

Category Description	BEAM, RA, EDGE, & PARALLEL CLAMPS
Type	Pre-assembled O.D. pipe and conduit clamp

### Packaging

Carton	1
Package	40
Weight Per each	0.56



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

7520 Eastgate Blvd Suite 100  
37122-0000, TN Mt. Juliet  
Phone: 615-257-4146  
Fax: 615-257-4147

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Mounting	CHANNEL
standard	Not Applicable