



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## B2208PAZN BLTD 1/2" ZN PLT Pa Unv Pipe Clamp

*Cooper B-Line/Cable Tray*

Catalog Number	B2208PAZN
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Multi-Grip and Offset Pipe Clamp, 0.0625" H X 2.1560" L X 1.25" W, Steel, 400 LBS Load Cap
Weight per unit	0.1200 (lbs/each)
Product Category	Channel & Strut Fittings

### Features

dimensions	2.1560 IN X 1.2500 IN X 0.0625 IN
Material	16 Gauge Low Carbon Steel

### Material, Color, and Finish

Finish	Zinc Plated
--------	-------------

### Dimensions and Weight

Size	1/2 in
------	--------

### Descriptions

Also Known As...	Strut Strut channel
Construction	TWO PIECE
Description	BLTD 1/2" ZN PLT PA UNV PIPE CLAMP
extra long description	B-LINE B2208PAZN 1/2"-MULTI-GRIP PI
Features	Eaton offers a wide variety of B-Line series pipe clamps and accessories used for the support and attachment of pipe to structural members.
Long Description	Eaton B-Line series multi-grip and offset pipe clamp, 0.0625" H x 2.1560" L x 1.25" W, Steel, 400 Lbs load cap
Product Type	1/2"-Multi-Grip Pipe Clamp, Pre-Asm, Thinwall
similar brands	Unistrut
Special Features	Includes Combination Recess Hex Head Machine Screw and Square Nut, Pipe Range 0.701 To 0.875 In OD, Load Capacity 400 Lb Vertical, 50 Lb Transverse

### Manufacturer Information

Brand	Eaton
GTIN	00781011604141
Manufacturers Part Number	B2208PAZN
UPC	781011604141

### Taxonomies, Classifications, and Categories

Category Description	STRUT CHANNEL
Type	Multi-grip and offset pipe clamp



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	100
Weight Per each	0.12

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Mounting	CHANNEL
standard	Not Applicable