



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## B2212PAZN BLTD 1-1/2" Zinc Plate Pre-Assemb Unv Pipe Clamp

*Cooper B-Line/Cable Tray*

Catalog Number	B2212PAZN
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Multi-Grip/Offset Pipe Clamp, 0.0966" H X 3.3750" L X 1.25" W, Steel, 600 LBS Load, Pipe Clamp For Thinwall (Emt)
Weight per unit	0.2300 (lbs/each)
Product Category	Channel & Strut Fittings

### Features

dimensions	3.3750 IN X 1.2500 IN X 0.0966 IN
Material	12 Gauge Low Carbon Steel

### Material, Color, and Finish

Finish	Pre-Galvanized
--------	----------------

### Dimensions and Weight

Size	1-1/2 in
------	----------

### Descriptions

Construction	TWO PIECE
Description	BLTD 1-1/2" ZINC PLATE PRE-ASSEMB UNV PIPE CLAMP
extra long description	B-LINE B2212PAZN 1 1/2" MULTI-GRIP
Features	Eaton offers a wide variety of B-Line series pipe clamps and accessories used for the support and attachment of pipe to structural members.
Long Description	Eaton B-Line series multi-grip/offset pipe clamp, 0.0966" H x 3.3750" L x 1.25" W, Steel, 600 Lbs load, Pipe clamp for thinwall (EMT)
Product Type	1 1/2" Multi-Grip Pipe Clamp, Pre-Asm, Thinwall
Special Features	Includes Combination Recess Hex Head Machine Screw and Square Nut, Pipe Range 1.735 To 1.931 In OD, Load Capacity 600 Lb Vertical, 75 Lb Transverse

### Manufacturer Information

Brand	Eaton
GTIN	00781011605445
Manufacturers Part Number	B2212PAZN
UPC	781011605445

### Taxonomies, Classifications, and Categories

Category Description	BEAM, RA, EDGE, & PARALLEL CLAMPS
Type	Multi-grip and offset pipe clamp



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.23

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Mounting	CHANNEL
standard	Not Applicable