



B2213PAZN BLTD 2" Zinc Plated Pre-Assembled Unv Pipe Clamp

Cooper B-Line/Cable Tray

Catalog Number	B2213PAZN
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Multi-Grip and Offset Pipe Clamp, 0.0966" H X 4" L X 1.25" W, Steel, 600 LBS Load Cap, Pipe Clamp For Thinwall (Emt)
Weight per unit	0.2600 (lbs/each)
Product Category	Channel & Strut Fittings

Features

dimensions	4.0000 IN X 1.2500 IN X 0.0966 IN
Material	12 Gauge Low Carbon Steel

Material, Color, and Finish

Finish	Zinc Plated
--------	-------------

Dimensions and Weight

Size	2 in
------	------

Descriptions

Construction	TWO PIECE
Description	BLTD 2" ZINC PLATED PRE-ASSEMBLED UNV PIPE CLAMP
extra long description	B-LINE B2213PAZN 2"-MULTI-GRIP PIPE
Features	Eaton offers a wide variety of B-Line series pipe clamps and accessories used for the support and attachment of pipe to structural members.
Long Description	Eaton B-Line series multi-grip and offset pipe clamp, 0.0966" H x 4" L x 1.25" W, Steel, 600 Lbs load cap, Pipe clamp for thinwall (EMT)
Product Type	2"-Multi-Grip Pipe Clamp, Pre-Asm, Thinwall IMC Rigid, 2", Z
Special Features	Includes Combination Recess Hex Head Machine Screw and Square Nut, Pipe Range 2.192 To 2.400 In OD, Load Capacity 600 Lb Vertical, 75 Lb Transverse

Manufacturer Information

Brand	Eaton
GTIN	00781011604646
Manufacturers Part Number	B2213PAZN
UPC	781011604646

Taxonomies, Classifications, and Categories

Category Description	BEAM, RA, EDGE, & PARALLEL CLAMPS
Type	Multi-grip and offset pipe clamp



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1811 N. University Suite 100
70507-0000, LA Lafayette
Phone: 337-235-7681
Fax: 337-235-7725

Packaging

Carton	1
Package	50
Weight Per each	0.26

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Mounting standard	CHANNEL
	Not Applicable