



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

8051 Bayberry Rd  
32256-0000, FL Jacksonville  
Phone: 904-339-8781  
Fax: 904-352-2616



## **B2350JR B-Cap Wire Connector, Model B2 Red, 350/Jar**

*Ideal*

Catalog Number	B2350JR
Manufacturer	Ideal
Description	Buchanan, Wire Connector, B-Cap, Conductor Range: 22 - 8 Awg, 2/18 Awg Min, 5/12 Awg Max, Number Of Conductors: 2 to 6, Material: Flame-Retardant Polypropelene, Color: Red, Voltage Rating: 600 V, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 F), Model Number: B2
Weight per unit	N/A
Product Category	Large Terminals & Connectors

### **Features**

Material	Flame-retardant Polypropelene
Voltage Rating	600

### **Material, Color, and Finish**

Color	Red
-------	-----



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

8051 Bayberry Rd  
32256-0000, FL Jacksonville  
Phone: 904-339-8781  
Fax: 904-352-2616

## Descriptions

Description	B-CAP WIRE CONNECTOR, MODEL B2 RED, 350/JAR
extra long description	IDEAL B2-350JR B-CAP B2 RED, 350 JA
Features	The B-CAP Wire Connector gets you in those hard-to reach spots comfortably, especially when you're retrofitting or updating. Slim, classic fins and an expanding interior spring give the B-CAP a secure grip with extra leverage, making it the most compact connector on the market for up to 5 #12 (Red Model B2).The unique, space-saving profile of the B-CAP makes it perfect for retrofit work and shallow boxes.The B-CAP also features a tough, flame-retardant shell that withstands environmental extremes with a de
Long Description	Buchanan, Wire Connector, B-CAP, Conductor Range: 22 - 8 AWG, 2/18 AWG Min, 5/12 AWG Max, Number Of Conductors: 2 to 6, Material: Flame-retardant Polypropelene, Color: Red, Voltage Rating: 600 V, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Model Number: B2
Product Type	B-Cap B2 Red, 350 Jar
Special Features	1,000V Maximum In Fixtures And Signs;Deep Skirt Protects Against Flash-Over And Turned-Back Strands For Maximum Dielectric Protection;Easily Removed For Repeat Usage On Same Size Or Larger Wire Combinations;Features: Classic Fin Design Provides Secure Grip For Extra Leverage On Maximum Wire Combinations;Green-B Designed For Making Ground Connections And Bonding Non-Metallic Sheathed Cable;Live-Action Spring Expands To Accept Wire Shape And Size No Pre-Twisting Required;Model Number: B2;Square-Wire Spring T

## Manufacturer Information

Brand	Buchanan
GTIN	00781789452005
Manufacturers Part Number	B2-350JR
UPC	781789452005

## Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
----------------------	--

## Availability

minimum qty	350
Status	Inactive



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

8051 Bayberry Rd  
32256-0000, FL Jacksonville  
Phone: 904-339-8781  
Fax: 904-352-2616

## Packaging

Carton	350
Package	2100
Weight Per each	0

## Uses, Certifications, and Standards

Application	Insulating or Joining 1 or more conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)
standard	CSA C22.2 #188, UL 486C Listed, RoHS