



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



B2350JR B-Cap Wire Connector, Model B2 Red, 350/Jar

Ideal

Catalog Number	B2350JR
Manufacturer	Ideal
Description	Buchanan, Wire Connector, B-Cap, Conductor Range: 22 - 8 Awg, 2/18 Awg Min, 5/12 Awg Max, Number Of Conductors: 2 to 6, Material: Flame-Retardant Polypropylene, Color: Red, Voltage Rating: 600 V, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 F), Model Number: B2
Weight per unit	0.0073 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Flame-Retardant Polypropylene
Number of Conductors	2 to 6
Voltage Rating	600

Material, Color, and Finish

Color	Red
-------	-----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	B-CAP WIRE CONNECTOR, MODEL B2 RED, 350/JAR
extra long description	IDEAL B2-350JR B-CAP B2 RED, 350 JA
Features	The B-CAP Wire Connector gets you in those hard-to reach spots comfortably, especially when you're retrofitting or updating. Slim, classic fins and an expanding interior spring give the B-CAP a secure grip with extra leverage, making it the most compact connector on the market for up to 5 #12 (Red Model B2).The unique, space-saving profile of the B-CAP makes it perfect for retrofit work and shallow boxes.The B-CAP also features a tough, flame-retardant shell that withstands environmental extremes with a de
Long Description	Buchanan, Wire Connector, B-CAP, Conductor Range: 22 - 8 AWG, 2/18 AWG Min, 5/12 AWG Max, Number Of Conductors: 2 to 6, Material: Flame-retardant Polypropelene, Color: Red, Voltage Rating: 600 V, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Model Number: B2
Product Type	B-Cap B2 Red, 350 Jar
Special Features	Features: Classic Fin Design Provides Secure Grip For Extra Leverage On Maximum Wire Combinations; Live-Action Spring Expands To Accept Wire Shape And Size No Pre-Twisting Required; Square-Wire Spring Threads Directly Onto Conductors For Fast, Secure Connections; Deep Skirt Protects Against Flash-Over And Turned-Back Strands For Maximum Dielectric Protection; Easily Removed For Repeat Usage On Same Size Or Larger Wire Combinations; Green-B Designed For Making Ground Connections And Bonding Non-Metallic She

Manufacturer Information

Brand	Buchanan
GTIN	00781789452005
Manufacturers Part Number	B2-350JR
sub brand	B-CAP ®
UPC	781789452005

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
----------------------	-----------

Availability

minimum qty	350
-------------	-----

Packaging

Carton	2100
Weight Per each	0.0073



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Insulating or Joining 1 or more conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)
standard	CSA C22.2 #188, UL 486C Listed, RoHS