



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3705 Lee Street
71302-0000, LA Alexandria
Phone: 318-445-1336
Fax: 318-445-8356



B4B B-Cap Wire Connector, Model B4 Blue/Gray, 250/Box

Ideal

Catalog Number	B4B
Manufacturer	Ideal
Description	Buchanan, Wire Connector, B-Cap, Conductor Range: 14 - 6 Awg, 2/12 Awg Min, 2/6 Awg Max, Number Of Conductors: 2 to 6, Material: Flame-Retardant Polypropelene, Color: Blue/Gray, Voltage Rating: 600 V, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 F), Model Number: B4
Weight per unit	0.0170 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Flame-retardant Polypropelene
Voltage Rating	600

Material, Color, and Finish

Color	Blue/Gray
-------	-----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3705 Lee Street
71302-0000, LA Alexandria
Phone: 318-445-1336
Fax: 318-445-8356

Descriptions

Description	B-CAP WIRE CONNECTOR, MODEL B4 BLUE/GRAY, 250/BOX
extra long description	IDEAL B4-B B-CAP B4 BLUE GRAY, 250
Features	The B-CAP Wire Connector gets you in those hard-to reach spots comfortably, especially when you're retrofitting or updating. Slim, classic fins and an expanding interior spring give the B-CAP a secure grip with extra leverage, making it the most compact connector on the market for up to 5 #12 (Red Model B2).The unique, space-saving profile of the B-CAP makes it perfect for retrofit work and shallow boxes.The B-CAP also features a tough, flame-retardant shell that withstands environmental extremes with a de
Long Description	Buchanan, Wire Connector, B-CAP, Conductor Range: 14 - 6 AWG, 2/12 AWG Min, 2/6 AWG Max, Number Of Conductors: 2 to 6, Material: Flame-retardant Polypropelene, Color: Blue/Gray, Voltage Rating: 600 V, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Model Number: B4
Product Type	B-Cap B4 Blue Gray, 250 CRTN
Special Features	1,000V Maximum In Fixtures And Signs;Deep Skirt Protects Against Flash-Over And Turned-Back Strands For Maximum Dielectric Protection;Easily Removed For Repeat Usage On Same Size Or Larger Wire Combinations;Features: Classic Fin Design Provides Secure Grip For Extra Leverage On Maximum Wire Combinations;Green-B Designed For Making Ground Connections And Bonding Non-Metallic Sheathed Cable;Live-Action Spring Expands To Accept Wire Shape And Size No Pre-Twisting Required;Model Number: B4;Square-Wire Spring T

Manufacturer Information

Brand	Buchanan
GTIN	00781789452043
Manufacturers Part Number	B4-B
UPC	781789452043

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
----------------------	--

Availability

minimum qty	250
-------------	-----

Packaging

Carton	250
Weight Per each	0.017



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3705 Lee Street
71302-0000, LA Alexandria
Phone: 318-445-1336
Fax: 318-445-8356

Uses, Certifications, and Standards

Application	Insulating or Joining 1 or more conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)
standard	CSA C22.2 #188, UL 486C Listed, RoHS