



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BAB1025 Type Bab Circuit BRKR, 1P, 25AMP, 40C, 120/240V, 10, 000 *Eaton Corp*

Catalog Number	BAB1025
Manufacturer	Eaton Corp
Description	Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, High Intensity Discharge, 25 A, 10 Kaic, Single-Pole, 120/240 V, Non-Interchangeable, Q7, Bab
Weight per unit	0.3500 (lbs/each)
Product Category	1 Pole Standard Trip Bolt-On

Features

amperage rating	25 A
dimensions	4.0000 IN X 1.0000 IN X 5.0000 IN
interrupt rating	10
media	Yes
Poles	1
Trip Type	Non-Interchangeable
Voltage Rating	120/240 V

Descriptions

Description	TYPE BAB CIRCUIT BRKR,1P,25AMP,40C,120/240V,10,000
extra long description	ETN BAB1025 BAB , 1P,25AMP,40C,120/2
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15–100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,High intensity discharge,25 A,10 kAIC,Single-pole,120/240 V,Non-Interchangeable,Q7,BAB
Product Type	Bab , 1P, 25AMP, 40C, 120/240V, 10ka
Special Features	High intensity discharge

Manufacturer Information

Brand	Eaton Corp
GTIN	00786679301258
Manufacturers Part Number	BAB1025
UPC	786679301258

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.35

Uses, Certifications, and Standards

Application	Datacenters - IT Space: CI and Hyper Converged Marine Vessels and Equipment - Marine Vessels and Equipment - Other OtherGeneration - Renewable Energy - Alternative EnergyGeneration - Conventional Energy - Conventional EnergyResidential Bldgs & Facilities - Residential Bldgs & Facilities - Other
standard	CSA Certified,UL Listed