



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **BAB1060 Type Bab Circuit BRKR 1P, 60AMP, 40C 120/240V, 10, 00a** *Eaton Corp*

|                  |  |
|------------------|--|
| Catalog Number   | BAB1060  |
| Manufacturer     | Eaton Corp   |
| Description      | Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Single-Pole, Non-Interchangeable, 60A, 10 Kaic, 120/240V |
| Weight per unit  | 1.0 (lbs/each)   |
| Product Category | 1 Pole Standard Trip Bolt-On   |

### **Features**

|                  |                                   |
|------------------|-----------------------------------|
| dimensions       | 3.7000 IN X 1.2000 IN X 4.6000 IN |
| interrupt rating | 10                                |
| media            | Yes                               |
| Poles            | Single-pole                       |
| Voltage Rating   | 120/240 V                         |

### **Descriptions**

|                        |  |
|------------------------|--|
| Description            | TYPE BAB CIRCUIT BRKR 1P,60AMP,40C 120/240V,10,00A   |
| extra long description | ETN BAB1060 BAB 1P,60AMP,40C, 120/2  |
| Features               | Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15-100A are HACR rated. Select from one-, two-, or three-pole designs. |
| Long Description       | Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Single-pole, Non-Interchangeable, 60A, 10 kAIC, 120/240V   |
| Product Type           | Bab 1P, 60AMP, 40C, 120/240V, 10, 00AIC,   |

### **Manufacturer Information**

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00786679301609 |
| Manufacturers Part Number | BAB1060        |
| UPC                       | 786679301609   |

### **Taxonomies, Classifications, and Categories**

|                      |                                   |
|----------------------|-----------------------------------|
| Category Description | PANELBOARD BRANCH BREAKERS        |
| Type                 | Thermal magnetic circuit breakers |

### **Packaging**

|                 |    |
|-----------------|----|
| Carton          | 1  |
| Package         | 24 |
| Weight Per each | 1  |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

OtherGeneration - Renewable Energy - Alternative  
EnergyGeneration - Conventional Energy - Conventional  
EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine  
Vessels and Equipment - Marine Vessels and Equipment -  
OtherResidential Bldgs & Facilities - Residential Bldgs & Facilities -  
Other

standard

CSA Certified,UL Listed