



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BAB2040 BAB2040 BRKR A

Eaton Corp

Catalog Number	BAB2040
Manufacturer	Eaton Corp
Description	Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, Bolt-On Mounting, High Intensity Discharge, 40 A, 10 Kaic, Two-Pole, 120/240 V, Non-Interchangeable, Q7, Bab
Weight per unit	0.6000 (lbs/each)
Product Category	2 Pole Standard Trip Bolt-On

Features

dimensions	3.1000 IN X 2.0000 IN X 2.9000 IN
interrupt rating	10
Poles	2
Voltage Rating	120/240 V

Descriptions

Description	BAB2040 BRKR A
extra long description	ETN BAB2040 BAB2040 BRKR A
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15–100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,Bolt-on mounting, High intensity discharge,40 A,10 kAIC,Two-pole,120/240 V,Non-Interchangeable,Q7,BAB
Product Type	BAB2040 BRKR A
Special Features	Bolt-on mounting

Manufacturer Information

Brand	Eaton
GTIN	00786679302408
Manufacturers Part Number	BAB2040
UPC	786679302408

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.6

Uses, Certifications, and Standards

Application	OtherGeneration - Renewable Energy - Alternative EnergyMarine Vessels and Equipment - Marine Vessels and Equipment - OtherGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedResidential Bldgs & Facilities - Residential Bldgs & Facilities - Other
standard	CSA Certified,UL Listed