



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1300 Hwy 34 South
75160-0000, TX Terrell
Phone: 972-563-2224
Fax: 972-563-2227



BAB1020S Bab BRKR 1P 20A Max 240V Max 10K Aic *Eaton Corp*

Catalog Number	BAB1020S
Manufacturer	Eaton Corp
Description	Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, 20 A, 10 Kaic, Single-Pole, 120/240 V, Non-Interchangeable, Q7, Bab, 24/48 VDC Shunt Trip
Weight per unit	1.0 (lbs/each)
Product Category	1 Pole Standard Trip Bolt-On

Features

dimensions	3.9000 IN X 2.2000 IN X 4.8000 IN
interrupt rating	10
media	Yes
Poles	1
Voltage Rating	120/240 V

Descriptions

Description	BAB BRKR 1P 20A MAX 240V MAX 10K AIC
extra long description	ETN BAB1020S BAB BREAKER 1P 20A MAX
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15–100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,20 A,10 kAIC,Single-pole,120/240 V,Non-Interchangeable,Q7,BAB,24/48 Vdc Shunt trip
Product Type	Bab Breaker 1P 20A Max 240V Max 10K Aic
Special Features	Bolt-on mounting

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786679509609
Manufacturers Part Number	BAB1020S
UPC	786679509609

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1300 Hwy 34 South
75160-0000, TX Terrell
Phone: 972-563-2224
Fax: 972-563-2227

Packaging

Carton	1
Weight Per each	1

Uses, Certifications, and Standards

Application	Generation - Conventional Energy - Conventional EnergyOtherMarine Vessels and Equipment - Marine Vessels and Equipment - OtherGeneration - Renewable Energy - Alternative EnergyDatacenters - IT Space: CI and Hyper ConvergedResidential Bldgs & Facilities - Residential Bldgs & Facilities - Other
standard	UL Listed,CSA Certified