



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

425 East Germann Road Suite 101
85297-0000, AZ Gilbert
Phone: 602-325-9757
Fax: 602-325-9758



BAB3025H BAB3025H BRKR A

Eaton Corp

Catalog Number	BAB3025H
Manufacturer	Eaton Corp
Description	Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial, 25A, 10 Kaic, Bolt-On Mounting, Three-Pole, Non-Interchangeable, 240V
Weight per unit	1.0 (lbs/each)
Product Category	3 Pole Standard Trip Bolt-On

Features

dimensions	3.5000 IN X 3.2000 IN X 3.0000 IN
interrupt rating	10
Poles	Three-pole
Voltage Rating	240 V - 240 V

Descriptions

Description	BAB3025H BRKR A
extra long description	ETN BAB3025H BAB3025H BRKR A
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15-100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton BAB thermal magnetic circuit breaker, Quicklag Industrial, 25A, 10 kAIC, Bolt-on mounting, Three-pole, Non-Interchangeable, 240V
Product Type	BAB3025H BRKR A
Special Features	Bolt-on mounting

Manufacturer Information

Brand	Eaton
GTIN	00786679303252
Manufacturers Part Number	BAB3025H
UPC	786679303252

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Package	8
Weight Per each	1



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

425 East Germann Road Suite 101
85297-0000, AZ Gilbert
Phone: 602-325-9757
Fax: 602-325-9758

Uses, Certifications, and Standards

Application

OtherGeneration - Renewable Energy - Alternative
EnergyGeneration - Conventional Energy - Conventional
EnergyMarine Vessels and Equipment - Marine Vessels and
Equipment - OtherDatacenters - IT Space: CI and Hyper
ConvergedResidential Bldgs & Facilities - Residential Bldgs &
Facilities - Other

standard

UL Listed,CSA Certified