



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BAB3050H Bab 3-Pole 50A BRKR

Eaton Corp

| | |
|------------------|---|
| Catalog Number | BAB3050H |
| Manufacturer | Eaton Corp |
| Description | Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, 50 A, 10 Kaic, Three-Pole, 240 V, Interchangeable, Bab, Distribution Panels 240V (Three-Phase, Four-Wire Maximum), Four-Wire, Three-Phase |
| Weight per unit | 1.0 (lbs/each) |
| Product Category | 3 Pole Standard Trip Bolt-On |

Features

| | |
|------------------|-----------------------------------|
| dimensions | 3.8000 IN X 3.2000 IN X 4.9000 IN |
| interrupt rating | 10 |
| media | Yes |
| Poles | 3 |
| Voltage Rating | 240 V - 240 V |

Descriptions

| | |
|------------------------|--|
| Description | BAB 3-POLE 50A BRKR |
| extra long description | ETN BAB3050H BAB 3-Pole 50 Amp Brea |
| Features | Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15-100A are HACR rated. Select from one-, two-, or three-pole designs. |
| Long Description | Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,50 A,10 kAIC,Three-pole,240 V,Interchangeable,BAB,Distribution panels 240V (Three-phase, four-wire maximum),Four-wire,Three-phase |
| Product Type | Bab 3-Pole 50 Amp Breaker |
| Special Features | Bolt-on mounting |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton |
| GTIN | 00786679303504 |
| Manufacturers Part Number | BAB3050H |
| UPC | 786679303504 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | PANELBOARD BRANCH BREAKERS |
| Type | Thermal magnetic circuit breakers |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status Inactive

Packaging

Carton 1

Weight Per each 1

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | Generation - Renewable Energy - Alternative Energy Marine Vessels and Equipment - Marine Vessels and Equipment - Other Other Datacenters - IT Space: CI and Hyper Converged Generation - Conventional Energy - Conventional Energy Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other |
| standard | UL Listed, CSA Certified |