



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **BAB3050H Bab 3-Pole 50A BRKR**

*Eaton Corp*

Catalog Number	BAB3050H
Manufacturer	Eaton Corp
Description	Eaton Bab Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, 50 A, 10 Kaic, Three-Pole, 240 V, Interchangeable, Bab, Distribution Panels 240V (Three-Phase, Four-Wire Maximum), Four-Wire, Three-Phase
Weight per unit	1.0 (lbs/each)
Product Category	3 Pole Standard Trip Bolt-On

### **Features**

dimensions	3.8000 IN X 3.2000 IN X 4.9000 IN
interrupt rating	10
media	Yes
Poles	Three-pole
Voltage Rating	240 V - 240 V

### **Descriptions**

Description	BAB 3-POLE 50A BRKR
extra long description	ETN BAB3050H BAB 3-Pole 50 Amp Brea
Features	Eaton's bolt-on miniature circuit breakers (Quicklag) provide superior protection in panelboards, and offer easy installation. They are also switching duty rated for 120 VAC fluorescent light applications, and UL 489 listed. All products 15–100A are HACR rated. Select from one-, two-, or three-pole designs.
Long Description	Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,50 A,10 kAIC,Three-pole,240 V,Interchangeable,BAB,Distribution panels 240V (Three-phase, four-wire maximum),Four-wire,Three-phase
Product Type	Bab 3-Pole 50 Amp Breaker
Special Features	Bolt-on mounting

### **Manufacturer Information**

Brand	Eaton
GTIN	00786679303504
Manufacturers Part Number	BAB3050H
UPC	786679303504

### **Taxonomies, Classifications, and Categories**

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Availability

Status ..... Inactive

## Packaging

Carton ..... 1

Weight Per each ..... 1

## Uses, Certifications, and Standards

Application ..... Generation - Renewable Energy - Alternative Energy  
Marine Vessels and Equipment - Marine Vessels and Equipment -  
OtherOtherDatacenters - IT Space: CI and Hyper  
ConvergedGeneration - Conventional Energy - Conventional  
EnergyResidential Bldgs & Facilities - Residential Bldgs & Facilities  
- Other

standard ..... UL Listed, CSA Certified