



Wall Studs




Box Mounting Bracket

- Supports boxes or plaster rings between studs 16" or 24" on center.
- Accepts US & Canadian boxes.
- Accommodates 4" or 4^{11/16}" boxes.
- Allows side-by-side mounting of 1^{1/2}" or 2^{1/8}" deep boxes.
- See Ruff-IN™ brochure for pre-fab box assemblies.
- Finish: Pre-galvanized



BB8-16




BB8-24



UPC/Part Number	Catalog Number	Description	Box Qty.
781011 02898	BB8-16	16" Stud Spacing	25
781011 02900	BB8-24	24" Stud Spacing	25

Read safety/installation instruction sheets in packages before use. These products are designed for positioning only. No load rating.

- Open box Support secures boxes and plaster rings between studs 16" and 24" on center.
- Accommodates 4", 4^{11/16}" and multi-gang boxes.
- Open design allows infinite adjustability - box can be placed in any horizontal position along the bracket.
- Stamped markings at 1/4", 1/2" and 1" increments allow the installer to easily locate the desired box position.
- See Ruff-IN™ brochure for pre-fab box assemblies.
- Finish: Pre-galvanized



Open Box Mounting Bracket




UPC/Part Number	Catalog Number	Description	Box Qty.
782051 45325	BB7-16	16" Stud Spacing	25
782051 45328	BB7-24	24" Stud Spacing	25

Read safety/installation instruction sheets in packages before use. These products are designed for positioning only. No load rating.

Wall Studs

- New BBF floorstand provides the most rigid support in the industry.
- Far-side support accommodates 6", 5 1/2", 3 5/8", and 2 1/2" stud depths.
- Fold-out tab built-in to attach floor stand to stud if desired.
- Integral "wings" provide rigid support when floorstand is mounted between studs.
- Optional cable containment clip securely attaches to floorstand without hardware.
- Patented Marty Mouse™ ears enable boxes to be secured in place with or without the plaster rings.
- Finish: Pre-galvanized.
- See Ruff-IN™ brochure for pre-fab box assemblies.




Floor-Mount Box Support


Wall Studs



BBFC



BBF15



BBF18



BBF24




BBFxxC

UPC/Part Number	Catalog Number	Box Center Height	Box Qty.
782051 52944	BBF15	15" Floorstand	25
782051 52945	BBF18	18" Floorstand	25
782051 52946	BBF24	24" Floorstand	25
782051 52947	BBFC	Cable Clip	25
782051 52948	BBF15C	15" Floorstand with Cable Clip	25
782051 52949	BBF18C	18" Floorstand with Cable Clip	25
782051 52950	BBF24C	24" Floorstand with Cable Clip	25

Patent # 5595362
Patent # 7956285 B2

Read safety/installation instruction sheets in packages before use. These products are designed for positioning only. No load rating.

- See **BBF Series** for a better solution.
- Provides support for electrical box from floor track or concrete forms.
- 18" length with break-away feature for 12" or 16" box mounting.
- Finish: Pre-galvanized




Floor Mounted Box Support



UPC/Part Number	Catalog Number	Description	Box Qty.
781011 03623	BB-18	Floor Mounted Box Support	50

- Attaches 13/16" strut, 1 1/2" lathers channel, 1/2" EMT or 3/4" EMT to metal studs.
- Provides support for vertical runs of conduit.
- Finish: Pre-galvanized



Strut Mounting Brackets

UPC/Part Number	Catalog Number	Description	Box Qty.
781011 01658	BMB1	Strut Mounting Bracket	25 pr.

Read safety/installation instruction sheets in packages before use. These products are designed for positioning only. No load rating.