



**USI ELECTRIC** brings over four decades of manufacturing expertise to a full line of safety products designed for the electrical industry.



**BFB-926**

**CEILING FAN & LIGHTING FIXTURE BRACE**

- **Designed for New or Existing Construction**  
Positioning Tabs for Accurate 1/2" Sheetrock Use  
Break Off Tabs for 3/4" and 1" Sheetrock Use
- **Strain Relief Mounting Hardware & Ground Screw Included**  
(8) #10 Phillips Case Hardened Screws 16 x 1 "  
(2) #10 Phillips Slotted Case Hardened Screws 32 x 2<sup>1/4</sup>"
- **Includes Steel Channel Hanger Bar**  
Adjustable for 16" to 24" Joists
- **Includes Steel Electrical Box**  
16 cu. in. Wiring Capacity  
(7) 7/8" Romex or Conduit Knockouts
- **Dual Purpose for**  
Ceiling Fans and Lighting Fixtures
- **Weight Limitations:**  
-- **70 lbs Ceiling Fans.** 35 lbs. when fan is > 16"  
-- **110 lbs. Lighting Fixtures.** 50 lbs. when fan is > 16"
- **Fast & Easy to Install**  
No Tools Required for Brace Expansion



Model No.	Box Size	Box Weight		Cube	Quantity M/C	UPC #
	inches	lbs.	kg.			
BFB-926 (24 pcs)	15.75 x 14.57 x 11.81	44.1	20.0	1.90 Ft. <sup>3</sup>	24	0-42741-00926-3

**USI ELECTRIC, INC.**  
 11407A CRONHILL DRIVE | OWINGS MILLS, MARYLAND 21117 USA  
 800.390.4321 | FAX 410.363.2218 | E-MAIL sales@usielectric.com  
[www.UsiElectric.com](http://www.UsiElectric.com)



**USI ELECTRIC** brings over four decades of manufacturing expertise to a full line of safety products designed for the electrical industry.



**BFB-926**  
**CEILING FAN & LIGHTING FIXTURE BRACE**

- **Designed for New or Existing Construction**  
 Positioning Tabs for Accurate 1/2" Sheetrock Use  
 Break Off Tabs for 3/4" and 1" Sheetrock Use
- **Strain Relief Mounting Hardware & Ground Screw Included**  
 (8) #10 Phillips Case Hardened Screws 16 x 1 "  
 (2) #10 Phillips Slotted Case Hardened Screws 32 x 2<sup>1/4</sup>"
- **Includes Steel Channel Hanger Bar**  
 Adjustable for 16" to 24" Joists
- **Includes Steel Electrical Box**  
 16 cu. in. Wiring Capacity  
 (7) 7/8" Romex or Conduit Knockouts
- **Dual Purpose for**  
 Ceiling Fans and Lighting Fixtures
- **Weight Limitations:**  
 -- **70 lbs Ceiling Fans.** 35 lbs. when fan is > 16"  
 -- **110 lbs. Lighting Fixtures.** 50 lbs. when fan is > 16"
- **Fast & Easy to Install**  
 No Tools Required for Brace Expansion



Model No.	Box Size	Box Weight		Cube	Quantity M/C	UPC #
	inches	lbs.	kg.			
BFB-926 (24 pcs)	15.75 x 14.57 x 11.81	44.1	20.0	1.90 Ft. <sup>3</sup>	24	0-42741-00926-3

**USI ELECTRIC, INC.**  
 11407A CRONHILL DRIVE | OWINGS MILLS, MARYLAND 21117 USA  
 800.390.4321 | FAX 410.363.2218 | E-MAIL sales@usielectric.com  
[www.UsiElectric.com](http://www.UsiElectric.com)