



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BIT600 600-4, 1-Sided Uni-Tap *Burndy LLC*

Catalog Number	BIT600
Manufacturer	Burndy LLC
Description	Aluminum Multiple Tap Connector, Clear Insulated, 2 Port, 1 Sided Entry, 4 Awg-600 Kcmil, Al/Cu Rated.
Weight per unit	0.4700 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Conductor Size	4 AWG-600 KCMIL
Insulation Type	Plastisol
Material	Aluminum
Operating Voltage	600 V

Descriptions

Description	600-4, 1-SIDED UNI-TAP
extra long description	BUR BIT600 600-4 ONE SIDE UNITAP
Long Description	Aluminum Multiple Tap Connector, Clear Insulated, 2 Port, 1 Sided Entry, 4 AWG-600 kcmil, Al/Cu Rated.
Product Type	RUN/TAP
Special Features	Features: Clear Plastisol Covered AL6061-T6 Aluminum Body: Saves Time, Lowers Installation Costs, Eliminates Taping, Clear Plastisol: Allows Visual Confirmation That Conductor Is Properly Inserted, Oxide Inhibitor Pre-Installed: Inhibits Moisture And Contaminants From Entering The Contact Area, Range-Taking: Reduces Number Of Connectors Carried In Inventory, Wire Entry: 1 or 2, Torque: 375 IN-LB, Hex Size (key): 3/8 IN, Conductor Size (run - Range): 4 AWG - 600 KCMIL, Type Of Insulation: Plastisol, Wire St

Manufacturer Information

Brand	BURNDY
GTIN	00781810225257
Manufacturers Part Number	BIT600
sub brand	UNITAP
UPC	781810225257

Taxonomies, Classifications, and Categories

Category Description	TERMINAL BLOCK ACESSORIES
Type	BIT



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	100
Weight Per each	0.47

Uses, Certifications, and Standards

Application	For Indoor Use Only, Copper Or Stranded Aluminum
standard	UL 486A-486B
Temperature Rating	90°C