



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BJ3125 Type BJ BRKR 125A/3 Pole 240V 10K Req 6 Spaces

Eaton Corp

Catalog Number	BJ3125
Manufacturer	Eaton Corp
Description	Eaton Type BJ 1-Inch Plug-On Main Breakers, Type BJ 1-Inch Plug-On Main Breakers, 125 A, 10 Kaic, Three-Pole, 240V, BJ, Common Breaker Trip, #2 Awg-300 Kcmil Cu/Al, BJ
Weight per unit	3.2 (lbs/each)
Product Category	3 Pole Standard Trip Plug-In

Features

amperage rating	125 A
dimensions	8.0000 IN X 3.5000 IN X 3.5000 IN
interrupt rating	10 kAIC
Poles	Three-pole
Trip Type	Common breaker trip
Voltage Rating	240 V - 240 V

Descriptions

Description	TYPE BJ BRKR 125A/3 POLE 240V 10K REQ 6 SPACES
extra long description	ETN BJ3125 BJ 125A/3 Pole 240V 10K
Features	Eaton's residential BR Circuit Breakers are used in load centers, panelboards, or similar devices. They are made for a wide range of applications and include: BR 1" circuit breakers and accessories for BR-style load centers; arc fault circuit interrupters (AFCI); and ground fault circuit interrupters (GFCI).
Long Description	Eaton Type BJ 1-Inch Plug-on Main Breakers, Type BJ 1-Inch plug-on main breakers, 125 A, 10 kAIC, Three-pole, 240V, BJ, Common breaker trip, #2 AWG-300 kcmil Cu/Al, BJ
Product Type	BJ 125A/3 Pole 240V 10K

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786676368308
Manufacturers Part Number	BJ3125
UPC	786676368308

Taxonomies, Classifications, and Categories

Category Description	Breaker Enclosures with or without Breaker
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Weight Per each	3.2



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Generation - Renewable Energy - Alternative Energy
Generation - Conventional Energy - Conventional Energy
Other Marine Vessels
and Equipment - Marine Vessels and Equipment -
Other Datacenters - IT Space: CI and Hyper Converged

standard

UL 489, Federal Specifications Classification W-C375