



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **BQC215230 BQC Quad BRKR 1-15A/2P 1-30A/2P Com. Trip 120/240V**

*Eaton Corp*

|                  |  |
|------------------|--|
| Catalog Number   | BQC215230  |
| Manufacturer     | Eaton Corp   |
| Description      | Eaton BR Thermal Magnetic Circuit Breaker, Type BQC 1-Inch CTL Plug-On Circuit Breaker, Includes Rejection Tab Feature, (1) Two-Pole 15 A, (1) Two-Pole 30 A, 10 Kaic, Four-Pole, 120/240V, BQC, Common Breaker Trip, #14-4 Awg Cu/Al, BQC |
| Weight per unit  | 0.8000 (lbs/each)  |
| Product Category | Quadplex Standard Trip Plug-In   |

### **Features**

|                  |                                    |
|------------------|------------------------------------|
| amperage rating  | (1) Two-Pole 15A, (1) Two-Pole 30A |
| dimensions       | 3.0000 IN X 2.0000 IN X 3.0000 IN  |
| interrupt rating | 10 kAIC                            |
| Poles            | Four-pole                          |
| Trip Type        | Common breaker trip                |
| Voltage Rating   | 120/240 V                          |

### **Descriptions**

|                        |   |
|------------------------|---|
| Description            | BQC QUAD BRKR 1-15A/2P 1-30A/2P COM. TRIP 120/240V  |
| extra long description | ETN BQC215230 BQC Quad 1-15A/2P 1-3   |
| Features               | Eaton's residential BR Circuit Breakers are used in load centers, panelboards, or similar devices. They are made for a wide range of applications and include: BR 1" circuit breakers and accessories for BR-style load centers; arc fault circuit interrupters (AFCI); and ground fault circuit interrupters (GFCI). |
| Long Description       | Eaton BR thermal magnetic circuit breaker, Type BQC 1-Inch CTL plug-on circuit breaker, Includes rejection tab feature, (1) Two-Pole 15 A, (1) Two-Pole 30 A, 10 kAIC, Four-pole, 120/240V, BQC, Common breaker trip, #14-4 AWG Cu/Al, BQC  |
| Product Type           | BQC Quad 1-15A/2P 1-30A/2P 120/240V 10K   |
| Special Features       | Includes Rejection Tab feature  |

### **Manufacturer Information**

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00786676006002 |
| Manufacturers Part Number | BQC215230      |
| UPC                       | 786676006002   |

### **Taxonomies, Classifications, and Categories**

|                      |   |
|----------------------|---|
| Category Description | Specialty Breakers (Quad, Dupl, Shunt Trip) |
| Type                 | Thermal magnetic circuit breakers           |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Weight Per each | 0.8 |

## Uses, Certifications, and Standards

|             |   |
|-------------|---|
| Application | OtherGeneration - Renewable Energy - Alternative<br>EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine<br>Vessels and Equipment - Marine Vessels and Equipment -<br>OtherGeneration - Conventional Energy - Conventional Energy |
| standard    | UL 489,Federal Specifications Classification W-C375   |