



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BR20STWTR Edge, Dup RCPT, Com, TR, 20A 125V, WH *Hubbell Wiring Devices*

Catalog Number	BR20STWTR
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Edgeconnect™, Duplex Receptacle, Commercial Grade, Tamper Resistant, 2-Pole 3-Wire, 20A 125V, 5-20R, Screwless Terminal, White
Weight per unit	0.2000 (lbs/each)
Product Category	Wiring Devices

### Features

connection	2-Pole, 3 Wire
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	3-Wire
pallet quantity	4000
Phase	1
Poles	2-Pole
Voltage Rating	125 V
Wire Size	#14 to #10

### Dimensions and Weight

Size	Standard Sized Product
------	------------------------

### Descriptions

Description	EDGE, DUP RCPT, COM, TR, 20A 125V, WH
extra long description	HWDK BR20STWTR EDGE, DUP RCPT, COM,
Features	EdgeConnect™ Screwless Termination system, simply insert the wire and press the plunger down. No tools are required. That connection is fool-proof and long lasting, to all but guarantee a high quality result. Any qualified installer regardless of level of training can guarantee a high quality result. Elapsed time? About 11 seconds!
Long Description	Straight Blade Devices, EdgeConnect™, Duplex Receptacle, Commercial Grade, Tamper Resistant, 2-Pole 3-Wire, 20A 125V, 5-20R, Screwless Terminal, White
Product Type	Edge, Dup RCPT, Com, TR, 20A 125V, WH
Special Features	EdgeConnect™ Technology, Screwless Termination



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585728056
Manufacturers Part Number	BR20STWTR
series	EdgeConnect™
UPC	783585728056

## Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Tamper-Resistant

## Packaging

Carton	1
Package	10
Weight Per each	0.2

## Uses, Certifications, and Standards

Application	Commercial Specification Grade
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	5-20R
standard	Certified to CSA 22.2, No. 42 File 285;NEMA® WD-6 Compliant;UL Listed to UL498 File No. E2186