

Specifications



Photo is representative

Eaton BRCAF115QN

Eaton BR AFI circuit breaker, Type BRC 1-Inch Combination AFI Circuit Breaker Arc Fault, Single-Pole, 15A, 120V, 10 kAIC, #14-4 AWG Cu/Al at 60°C or 75°C, Arc fault, Quick Connect Neutral

General specifications

PRODUCT NAME	Eaton BR AFI circuit breaker
CATALOG NUMBER	BRCAF115QN
UPC	786685952697
PRODUCT LENGTH/DEPTH	5 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	3 in
PRODUCT WEIGHT	0.45 lb
WARRANTY	Limited lifetime residential, 1 year commercial
CERTIFICATIONS	Contact Manufacturer



Powering Business Worldwide

Product specifications

TYPE AFCI circuit breakers

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - BRCAF115QN](#)

WARRANTY GUIDES

[Eaton type BR circuit breaker limited warranty June 2024](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative

Eaton BRCAF115QN

Eaton BR AFI circuit breaker, Type BRC 1-Inch Combination AFI Circuit Breaker Arc Fault, Single-Pole, 15A, 120V, 10 kAIC, #14-4 AWG Cu/Al at 60°C or 75°C, Arc fault, Quick Connect Neutral

General specifications

PRODUCT NAME	Eaton BR AFI circuit breaker
CATALOG NUMBER	BRCAF115QN
UPC	786685952697
PRODUCT LENGTH/DEPTH	5 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	3 in
PRODUCT WEIGHT	0.45 lb
WARRANTY	Limited lifetime residential, 1 year commercial
CERTIFICATIONS	Contact Manufacturer



Powering Business Worldwide

Product specifications

TYPE AFCI circuit breakers

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - BRCAF115QN](#)

WARRANTY GUIDES

[Eaton type BR circuit breaker limited warranty June 2024](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

