ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

BRDC230230 BRDC BRKR 2-30A/2P Com. Trip 120/240V 10K Non-CTL

Eaton Corp

Catalog Number	BRDC230230
Manufacturer	Eaton Corp
Description	Eaton BR Thermal Magnetic Circuit Breaker, Type BR 1-Inch Quad Circuit Breaker, (2) 30 A, (2) 30 A, 10 Kaic, Four-Pole, 120/240V, BRD, Common Breaker Trip, #14-4 Awg Cu/Al, BRD, Type BR Loadcenters
Weight per unit	0.8000 (lbs/each)
Product Category	Quadplex Standard Trip Plug-In

Features

dimensions	3.0000 IN X 2.0000 IN X 3.0000 IN
interrupt rating	10 kAIC
Poles	Four-pole
Trip Type	Common breaker trip
Voltage Rating	120/240 V

Descriptions

Description	BRDC BRKR 2-30A/2P COM. TRIP 120/240V 10K NON-CTL
extra long description	ETN BRDC230230 Eaton BR thermal mag
Features	Eaton's residential BR Circuit Breakers are used in load centers, panelboards, or similar devices. They are made for a wide range of applications and include: BR 1" circuit breakers and accessories for BR-style load centers; arc fault circuit interrupters (AFCI); and ground fault circuit interrupters (GFCI).
Long Description	Eaton BR thermal magnetic circuit breaker,Type BR 1-Inch quad circuit breaker,(2) 30 A, (2) 30 A,10 kAIC,Four-pole,120/240V,BRD,Common breaker trip,#14-4 AWG Cu/Al,BRD,Type BR Loadcenters
Product Type	Eaton BR Thermal Magnetic Circuit Breaker

Manufacturer Information

Brand	Eaton
GTIN	00786676372329
Manufacturers Part Number	BRDC230230
UPC	786676372329

Taxonomies, Classifications, and Categories

Category Description	Specialty Breakers (Quad, Dupl, Shunt Trip)
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Weight Per each	0.8

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	OtherGeneration - Renewable Energy - Alternative EnergyGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - Other
standard	UL 489,Federal Specifications Classification W-C375