

# Eaton BR816L125FP

Catalog Number: BR816L125FP

Eaton Eaton BR main lug loadcenter ,Ground bar, current design,Main lug,125 A,7R,Aluminum,Cover included,NEMA 3R,Metallic,10 kAIC,BR,NEMA 3R,12 Circuits,Twenty-four pole,6 Spaces,Three-wire,Single-phase



## General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BR816L125FP
UPC	Product Length/Depth
786676002110	3.56 in
Product Height	Product Width
13 in	11 in
Product Weight	Warranty
12 lb	10 year
Certifications	
UL 50	
UL 67	

## defaultTaxonomyAttributeLabel

### Special features

Current design

### Type

Main lug

### Amperage Rating

125 A

### Bus material

Aluminum

### Cover

Cover not included

### Main circuit breaker

BR

### Mounting

Flush

### Number of circuits

16

### Number of spaces

8

### Phase

Single-phase

### Voltage rating

120/240V

### Wire size

#14-1 AWG Cu/Al

### Box size

7

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

[Type BR Arc Fault Circuit Breakers and Loadcenters](#)

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Installation instructions

[Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)

### Specifications and datasheets

[Eaton Specification Sheet - BR816L125FP](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton BR816L125FP

Catalog Number: BR816L125FP

Eaton Eaton BR main lug loadcenter ,Ground bar, current design,Main lug,125 A,7R,Aluminum,Cover included,NEMA 3R,Metallic,10 kAIC,BR,NEMA 3R,12 Circuits,Twenty-four pole,6 Spaces,Three-wire,Single-phase



## General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BR816L125FP
UPC	Product Length/Depth
786676002110	3.56 in
Product Height	Product Width
13 in	11 in
Product Weight	Warranty
12 lb	10 year
Certifications	
UL 50	
UL 67	

## defaultTaxonomyAttributeLabel

### Special features

Current design

### Type

Main lug

### Amperage Rating

125 A

### Bus material

Aluminum

### Cover

Cover not included

### Main circuit breaker

BR

### Mounting

Flush

### Number of circuits

16

### Number of spaces

8

### Phase

Single-phase

### Voltage rating

120/240V

### Wire size

#14-1 AWG Cu/Al

### Box size

7

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

[Type BR Arc Fault Circuit Breakers and Loadcenters](#)

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Installation instructions

[Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)

### Specifications and datasheets

[Eaton Specification Sheet - BR816L125FP](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)