



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

221 Hord St
70123-0000, LA Harahan
Phone: 504-264-9995
Fax: 504-264-5996



BT5LHC0 The BT5LH-C0 Dome-Top Barb Ty, Features A Unique *Panduit Corporation*

Catalog Number	BT5LHC0
Manufacturer	Panduit Corporation
Description	The BT5LH-C0 Dome-Top® Barb Ty, Features A Unique Patented Design With Its Round Smooth Edges. Paired With The Stainless Steel Locking Barb, These Cable Ties Provide Consistent Performance, Reliability and Infinite Adjustability Through The Entire Bundle Range. Light Heavy Cross Section 18.1" (460MM). Appropriate For Indoor/Outdoor Use, Made Of Weather Resistant Nylon 6.6 With High Resistance to Ultraviolet Light, Are Black In Color and Come In Packages Of 100.
Weight per unit	N/A
Product Category	Cable Ties & Wraps

Features

media	Yes
Tensile Strength	120

Dimensions and Weight

Length	18.1
Thickness	0.07

Descriptions

Description	THE BT5LH-C0 DOME-TOP BARB TY, FEATURES A UNIQUE
extra long description	PAN BT5LH-C0 Dome-Top® BT5LH-C0 Bar
Long Description	The BT5LH-C0 Dome-Top® barb ty, features a unique patented design with its round smooth edges. Paired with the stainless steel locking barb, these cable ties provide consistent performance, reliability and infinite adjustability through the entire bundle range. Light heavy cross section 18.1" (460mm). Appropriate for Indoor/Outdoor use, made of Weather Resistant Nylon 6.6 with high resistance to ultraviolet light, are black in color and come in packages of 100.
Product Type	Dome-Top® BT5LH-C0 Barb Tie, Black, Uv PA6.6, 18.1"L, 120LB,
Special Features	Indoor/Outdoor

Manufacturer Information

Brand	PANDUIT
GTIN	00074983412785
Manufacturers Part Number	BT5LH-C0
UPC	074983412785

Taxonomies, Classifications, and Categories

Type	Cable Tie
------	-----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

221 Hord St
70123-0000, LA Harahan
Phone: 504-264-9995
Fax: 504-264-5996

Packaging

Carton	100
Package	500
Weight Per each	0

Uses, Certifications, and Standards

standard	UL 62275 (File E56854), CSA-C22.2 No. 62275 (File 31212), Cert 05968/C0, BV File ACE 14/601/01 Product Code: 2535H, 89/60111 (E3), 11130200, QPL-AS23190, RoHS Compliant
----------	--