



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BRP40N200G BR Pon Loadcntr 200A Convertible 40 Space Ground B

Eaton Corp

Catalog Number	BRP40N200G
Manufacturer	Eaton Corp
Description	Eaton BR Convertible Loadcenter, Ground Bar, Convertible, 200 A, X8, Aluminum, Cover Included, Nema 1, Metallic, 10 Kaic, CSR, Combination, 80 Circuits, Single-Pole, 40 Spaces, Two Hots, Neutral, and A Ground, Single-Phase, Type BR 1-Inch Breakers, 120/240 V
Weight per unit	33.6 (lbs/each)
Product Category	Single Phase Convertible Load

Features

amperage rating	200
Cover Type	Cover included
dimensions	39.0000 IN X 14.3100 IN X 3.8800 IN
interrupt rating	10 kAIC
number of spaces	40
Phase	1
Voltage Rating	120/240
Wattage	Single-pole

Dimensions and Weight

Size	X8
------	----

Descriptions

Description	BR PON LOADCNTR 200A CONVERTIBLE 40 SPACE GROUND B
Long Description	Eaton BR convertible loadcenter,Ground bar,Convertible,200 A,X8,Aluminum,Cover included,NEMA 1,Metallic,10 kAIC,CSR,Combination,80 Circuits,Single-pole,40 Spaces,Two hots, neutral, and a ground,Single-phase,Type BR 1-inch breakers,120/240 V
Product Type	Type BR 1-Inch Pon Loadcenter
Special Features	Ground bar

Manufacturer Information

Brand	EATON
GTIN	00786689053048
Manufacturers Part Number	BRP40N200G
UPC	786689053048

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
Type	Convertible loadcenter



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	33.6

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting	Combination
standard	UL 50,UL 67