ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

BT2SC0 8" Nyln CBL Tie SS Barb STD Cross Sec BLCK

Panduit Corporation

Catalog Number	BT2SC0
Manufacturer	Panduit Corporation
Description	The Dome-Top® BT2S-C0 Cable Tie Provides Dependable Bundling For Indoor/Outdoor Routing and Organization Requiring Uv and Weather Resistance. Standard Cross Section, 8 In (203MM) Long With 50 LB (222 N) Minimum Loop Tensile Strength and A 0.06–2 In (1.5–50.8MM) Bundle Diameter Range. It Is Black Nylon 6.6 (Uv-Resistant, Weather-Resistant). Operating Range -76 to 185°F (-60 to 85°C). Use With GTS-E, GS2B-E, GTH-E, GS4H-E, PTS, PTH, PPTS, STS2, and STH2 Tools.
Weight per unit	0.3470 (lbs/each)
Product Category	Cable Ties & Wraps

Features

media	Yes
Tensile Strength	50

Dimensions and Weight

Length	8
Thickness	0.05

Descriptions

Description	8" NYLN CBL TIE SS BARB STD CROSS SEC BLCK
extra long description	PAN BT2S-C0 Cable Tie, Black UV PA6
Long Description	The Dome-Top® BT2S-C0 cable tie provides dependable bundling for indoor/outdoor routing and organization requiring UV and weather resistance. Standard cross section, 8 in (203mm) long with 50 lb (222 N) minimum loop tensile strength and a 0.06–2 in (1.5–50.8mm) bundle diameter range. It is black Nylon 6.6 (UV-Resistant, Weather-Resistant). Operating range -76 to 185°F (-60 to 85°C). Use with GTS-E, GS2B-E, GTH-E, GS4H-E, PTS, PTH, PPTS, STS2, and STH2 tools.
Product Type	Cable Tie, Black Uv PA6.6, 8.0"L (203MM), 50LB, PK100
Special Features	Indoor/Outdoor

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	PANDUIT
GTIN	00074983411771
Manufacturers Part Number	BT2S-C0
UPC	074983411771

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Cable Tie

Availability

minimum qty	100

Packaging

Carton	100
Package	1000
Weight Per each	0.347

Uses, Certifications, and Standards

standard	UL 62275 (File E56854), CSA-C22.2 No. 62275, 11130200, NRC 10CFR50, QPL-AS23190, CSA Certified, RoHS Compliant