

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4955 Bell Springs Rd Unit 9 78620-0000, TX Dripping Springs Phone: 737-317-5073 Fax: 737-317-5074



C10 1/0 Cu Long Barrel Compression Butt Splice *Nsi Industries*

Catalog Number	C10
Manufacturer	Nsi Industries
Description	Long Barrel TINNEDCOPPERSPLICE1/0 Awg Long Barrel Tinned Coppersplices Is A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed.
Weight per unit	0.1100 (lbs/each)
Product Category	Large Terminals & Connectors
Features	
Material	Copper
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Material, Color, and Finish	
Color	Pink
Finish	Tin Plated
Dimensions and Weight	
Size	L=2.20 - OD=.519 - ID=.389



ELLIOTT ELECTRIC SUPPLY 4955 Bell Springs Rd Unit 9 78620-0000, TX Dripping Springs Phone: 737-317-5073 Fax: 737-317-5074

_			•			
. 1	es	~r	ın		$\boldsymbol{\wedge}$	nc
	_	LL		,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,		117
_	-	v.			•	

Description	1/0 CU LONG BARREL COMPRESSION BUTT SPLICE
extra long description	NSI C-1/0 1/0 AWG Copper Long Barre
Features	Long Barrel TinnedCopperSplice1/0 AWG Long Barrel Tinned CopperSplices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Long Description	Long Barrel TinnedCopperSplice1/0 AWG Long Barrel Tinned CopperSplices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Product Type	1/0 Awg Copper Long Barrel Splice - Pink
Special Features	1/0 AWG (STR) - CU Splice

Manufacturer Information

Brand	NSi
GTIN	00662381037558
Manufacturers Part Number	C-1/0
UPC	662381037558

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Long Barrel - CU Splice
rkaning	

Packaging

Carton	1	
Package	50	
Weight Per each	0.11	

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)
Temperature Rating	90 C