ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

C2 2" PVC TYPE C CONDULET

CANTEX,INC

Catalog Number	C2
Manufacturer	CANTEX,INC
Description	CANTEX 5133106 is a 2 in. Conduit Body Type C which provides pull, splice, and tap access for conductors in a conduit system
Weight per unit	1.6 (lbs/each)
Product Category	PVC Bodies & Boxes

Dimensions and Weight

Size	2

Descriptions

Description	2" PVC TYPE C CONDULET
Features	CANTEX 5133106 is a 2 in. Conduit Body Type C which provides pull, splice, and tap access for conductors in a conduit system
Long Description	CANTEX 5133106 is a 2 in. Conduit Body Type C which provides pull, splice, and tap access for conductors in a conduit system
Product Type	2 Ul Access FTG C
Extra Long Description	CTX 5133106 2 UL ACCESS FTG C

Manufacturer Information

Brand	PVC & Accessories CANTEX INC.
GTIN	00088700567634
Manufacturers Part Number	5133106
UPC	881780

Taxonomies, Classifications, and Categories

Category Description	PVC CONDULETS
Type	2 in. Conduit Body Type C

Trade Size

Trade Size	2

Packaging

Carton	1
Package	5
Weight Per Each	1.6 (lbs/each)

Uses, Certifications, and Standards

Standard	UL Listed;UL, Made in USA

Conduit Bodies

Conduit Bodies - Type C

1/2" THROUGH 2"

Conduit Body Type C provides pull, splice, and tap access for conductors in a conduit system. Type C Conduit Bodies have openings on each end and are for straight conduit run.

- Durable non-conductive PVC will not rust or corrode
- For use with Schedule 40 & 80 conduit
- Includes lid, gasket, and screws
- UL listed
- Made in USA



2-1/2" THROUGH 4"

Part Number	Trade Size	Carton Quantity	"A"	"B"	"C"	"D"	"E"	Volume Cu. In.	3-Wire Fill
5133101	1/2	25	1.938	1.500	4.625	4.000	.875	4.3	#6 or smaller
5133102	3/4	15	1.500	1.688	5.375	4.625	1.063	6.5	#6 or smaller
5133103	1	10	1.750	2.000	6.563	5.375	1.313	11.8	#6 or smaller
5133104	1-1/4	10	2.500	2.500	8.188	7.188	1.688	25.0	XHHW #1
5133105	1-1/2	10	2.625	2.813	9.250	8.000	1.938	36.5	XHHW #2/0
5133106	2	5	3.125	3.375	10.375	9.500	2.375	63.5	XHHW #4/0
5133108	2-1/2	5	4.625	4.625	19.000	12.875	2.875	198.0	XHHW 500 MCM
5133107	3	5	4.625	4.625	19.000	12.875	3.500	198.0	XHHW 500 MCM
5133110	3-1/2	4	5.563	5.563	20.375	13.750	4.000	305.0	XHHW 500 MCM
5133109	4	4	4.000	5.563	20.188	13.875	4.500	305.0	XHHW 500 MCM

Dimensions are nominal

SINGLE SOURCE FOR PVC ELECTRICAL

CANTEX offers a complete line of PVC Conduit Bodies as part of a full line PVC electrical products. The CANTEX Conduit Body line includes multiple sizes of Type LB, Type LL, Type LR, Type T, Type C, and Type E Conduit Bodies.

With several decades of experience manufacturing PVC conduit, fittings and accessories, you can trust CANTEX to provide quality products. To see our complete line of PVC Conduit Bodies or our full line of PVC electrical products visit www.cantexinc.com.