



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## C25HNE3120A 3P 120A 120V DP Contactor

*Eaton Corp*

Catalog Number	C25HNE3120A
Manufacturer	Eaton Corp
Description	
Weight per unit	8.7 (lbs/each)
Product Category	Definite Purpose Contactors

### Features

amperage rating	120A
coil	110-120 Vac, 50/60 Hz
dimensions	5.9400 IN X 3.5400 IN X 7.1700 IN
Enclosure Type	Open with metal mounting plate
Frame Size	120A, two- and three-pole
inductive full load	120A
Poles	Three-pole
resistive load	140A
terminals	Box lugs (posidrive setscrew)

### Dimensions and Weight

Size	120A, two- and three-pole
------	---------------------------

### Descriptions

Description	3P 120A 120V DP CONTACTOR
Product Type	DP Cont 120A 3P Opn 120V

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782114182413
Manufacturers Part Number	C25HNE3120A
Model	Contactors
UPC	782114182413

### Taxonomies, Classifications, and Categories

Category Description	DP CONTACTORS
igcc	4755
Type	NON-REVERSING
unspsc code	39121529

### Packaging

Carton	1
Weight Per each	8.7



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application .....	Motor and Power Control Equipment .....
Enclosure .....	Open with metal mounting plate .....
standard .....	UL Recognized; CSA Certified .....



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Definite Purpose Control - Contactor

**C25HNE3120A**

**UPC:**782114182413

### Dimensions:

- **Height:** 7.17 IN
- **Length:** 5.94 IN
- **Width:** 3.54 IN

**Weight:**8.5 LB

**Notes:**Resistive Load rating per pole

### Warranties:

- 1 year

### Specifications:

- **Amperage Rating:** 120A
- **Coil:** 110-120 Vac, 50/60 Hz
- **Enclosure:** Open with metal mounting plate
- **Frame Size:** 120A, two- and three-pole
- **Model:** Contactor
- **Number Of Poles:** Three-pole
- **Resistive Load:** 140A
- **Terminals:** Box lugs (posidrive setscrew)
- **Type:** Non-reversing

### Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [C25HNE3 3D Inventor](#)
- [C25HNE3AutoCAD 2D Footprint \(mm\)](#)
- [C25HNE3 2D PDF](#)
- [C25HNE3 2D Drawing Xchange](#)
- [C25HNE3 AutoCAD 2D Footprint](#)
- [C25HNE3 3D Model Xchange](#)
- [Eaton Specification Sheet - C25HNE3120A](#)

### Certifications:

- UL Recognized



- CSA Certified

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.