



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C25DNC330A Open N-R 3P 30A DP Cont SCR/PP W/O QC Term 120vac *Eaton Corp*

Catalog Number	C25DNC330A
Manufacturer	Eaton Corp
Description	Eaton Definite Purpose Contactor, Mounting Plate, Quick, Pressure Plate, 48 VDC, Open With Metal Mounting Plate, 15-50A, Two- and Three-Pole, Contactor, Three-Pole, Global Listed
Weight per unit	1.2 (lbs/each)
Product Category	Definite Purpose Contactors

Features

Coil Voltage	110-120 Vac, 50/60 Hz
connection	Quick
dimensions	3.3500 IN X 2.4000 IN X 3.7500 IN
Enclosure Type	Open with metal mounting plate

Dimensions and Weight

Size	15 - 50A, two-pole and three-pole
------	-----------------------------------

Descriptions

Description	OPEN N-R 3P 30A DP CONT SCR/PP W/O QC TERM 120VAC
extra long description	ETN C25DNC330A OP N-R 3P 30ADPCNT S
Features	Definite purpose contactors and starters are electrically operated switching devices specifically designed for the heating, ventilation, air conditioning and refrigeration (HVAC) industry.
Long Description	Eaton definite purpose contactor, Mounting plate, Quick, Pressure plate, 48 Vdc, Open with metal mounting plate, 15-50A, two- and three-pole, Contactor, Three-pole, Global listed
Product Type	Op N-R 3P 30ADPCNT SCR/PP W/O Qc120ac

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782116307371
Manufacturers Part Number	C25DNC330A
UPC	782116307371

Taxonomies, Classifications, and Categories

Category Description	DP CONTACTORS
Type	Definite purpose contactor

Packaging

Carton	1
Weight Per each	1.19



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & EOEM - Electrical Assemblies, Panels
and EOEMs

standard

UL Recognized, CSA Certified, UL Listed file E1491 (Guide Number
NLDX2), RoHS Compliant