



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2509 West 5th
79072-0000, TX Plainview
Phone: 806-296-5518
Fax: 806-291-0839



C2WH6 2" Wiring Duct Cover, White *Panduit Corporation*

Catalog Number	C2WH6
Manufacturer	Panduit Corporation
Description	The C2WH6 PVC Flush Wiring Duct Cover Features A Non-Slip, Liner to Prevent Cover Slide. Designed With The User In Mind, The Cover Is Easy to Install and Remove. The General-Purpose Lead-Free PVC Material Is Suitable For Use In Indoor Applications. UI 94 Flame Class Of V-0 With A UI Recognized Continuous-Use Temperature Up to 122°F (50°C). 0.35" X 2.25" (8.9 MM X 57.2 MM) and 6' (1.83 M) Long. Color White.
Weight per unit	0.1220 (lbs/each)
Product Category	Wiring Duct & Accessories

Features

connection	Snap-on
media	Yes

Material, Color, and Finish

Color	White
-------	-------

Dimensions and Weight

Length	NA
Width	2.25

Descriptions

Description	2" WIRING DUCT COVER, WHITE
extra long description	PAN C2WH6 Panduct® C2WH6 Flush Duct
Long Description	The C2WH6 PVC Flush Wiring Duct Cover features a non-slip, liner to prevent cover slide. Designed with the user in mind, the cover is easy to install and remove. The general-purpose lead-free PVC material is suitable for use in indoor applications. UL 94 flame class of V-0 with a UL recognized continuous-use temperature up to 122°F (50°C). 0.35" x 2.25" (8.9 mm x 57.2 mm) and 6' (1.83 m) long. Color White.
Product Type	Panduct® C2WH6 Flush Duct Cover

Manufacturer Information

Brand	PANDUIT
GTIN	00074983230822
Manufacturers Part Number	C2WH6
UPC	074983230822



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2509 West 5th
79072-0000, TX Plainview
Phone: 806-296-5518
Fax: 806-291-0839

Taxonomies, Classifications, and Categories

Category Description WIRE DUCT AND COVERS

Type Flushed Duct Cover

Availability

minimum qty 6

Packaging

Carton 120

Weight Per foot 0.122

Uses, Certifications, and Standards

Application Cover for Wiring Duct

standard CE Compliant;CSA Certified;Flammability Ratings: UL94 V-0;RoHS
Compliant;UL Recognized