

Specifications



Eaton CCP-1-30CC

Eaton Bussmann series RD non-fused rotary disconnect switch, Standard switch, Front handle operation, 600V, 1200A, Non-fused disconnect switch, CCP-1-30CC

General specifications

PRODUCT NAME	Eaton Bussmann series CCP UL98 fusible disconnect
CATALOG NUMBER	CCP-1-30CC
UPC	051712157858
PRODUCT LENGTH/DEPTH	3.65 in
PRODUCT HEIGHT	3.14 in
PRODUCT WIDTH	2.07 in
PRODUCT WEIGHT	2.16 lb
WARRANTY	Not Applicable
COMPLIANCES	Not Applicable RoHS Compliant
CERTIFICATIONS	Contact Manufacturer

Electrical rating

AMPERAGE RATING	30A
VOLTAGE RATING	600 Vac, 125 Vdc

Physical details

FUSE TYPE	Class CC
NUMBER OF POLES	Single-pole

Resources

MULTIMEDIA	Bussmann series Fuseology
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CCP-1-30CC

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Eaton CCP-1-30CC

Eaton Bussmann series RD non-fused rotary disconnect switch, Standard switch, Front handle operation, 600V, 1200A, Non-fused disconnect switch, CCP-1-30CC

General specifications

PRODUCT NAME	Eaton Bussmann series CCP UL98 fusible disconnect
CATALOG NUMBER	CCP-1-30CC
UPC	051712157858
PRODUCT LENGTH/DEPTH	3.65 in
PRODUCT HEIGHT	3.14 in
PRODUCT WIDTH	2.07 in
PRODUCT WEIGHT	2.16 lb
WARRANTY	Not Applicable
COMPLIANCES	Not Applicable RoHS Compliant
CERTIFICATIONS	Contact Manufacturer



Powering Business Worldwide

Electrical rating

AMPERAGE RATING	30A
VOLTAGE RATING	600 Vac, 125 Vdc

Physical details

FUSE TYPE	Class CC
NUMBER OF POLES	Single-pole

Resources

MULTIMEDIA	Bussmann series Fuseology
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CCP-1-30CC

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

