

Specifications



Eaton CFSR-2023

Eaton Crouse-Hinds series PowerGard replacement receptacle, 20A, Two-wire, three-pole, Copper-free aluminum, 125 Vac

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series PowerGard replacement receptacle
CATALOG NUMBER	CFSR-2023
UPC	662276358393
PRODUCT LENGTH/DEPTH	6.5 in
PRODUCT HEIGHT	6.5 in
PRODUCT WIDTH	6 in
PRODUCT WEIGHT	6.1 lb

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
----------------------------	--------------------------------

STANDARDS TYPE	NEC/CEC
-----------------------	---------

NEC HAZARDOUS RATING	Class I, Division 1 Class II, Division 1 Class III
-----------------------------	--

NEMA RATING	3 3R
--------------------	---------

Product specifications

CONFIGURATION	Two-wire, three-pole
----------------------	----------------------

AMPERAGE RATING	20A
------------------------	-----

VOLTAGE RATING	125 Vac
-----------------------	---------

MATERIAL	Copper-free aluminum
-----------------	----------------------

Resources

BROCHURES	PowerGard Explosionproof NEMA Locking Receptacles brochure
CATALOGS	PowerGard Explosionproof NEMA Locking Receptacles catalog page
	PowerGard Explosionproof NEMA Locking Receptacles Canadian certification (Receptacles with Plugs Interlocked with Switches)
	PowerGard Explosionproof NEMA Locking Receptacles Canadian certification (Receptacles with Plugs)
CERTIFICATION REPORTS	PowerGard Explosionproof NEMA Locking Receptacles UL certification (PowerGard Receptacles and Back Boxes Classified for use with Crouse-Hinds ENP Plugs)
	PowerGard Explosionproof NEMA Locking Receptacles UL certification (PowerGard Receptacles and Back Boxes Classified for use with Appleton ECP Plugs and EFS Receptacles)
INSTALLATION INSTRUCTIONS	IF 1663 - PowerGard Receptacles
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CFSR-2023

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Eaton CFSR-2023

Eaton Crouse-Hinds series PowerGard replacement receptacle, 20A, Two-wire, three-pole, Copper-free aluminum, 125 Vac

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series PowerGard replacement receptacle
CATALOG NUMBER	CFSR-2023
UPC	662276358393
PRODUCT LENGTH/DEPTH	6.5 in
PRODUCT HEIGHT	6.5 in
PRODUCT WIDTH	6 in
PRODUCT WEIGHT	6.1 lb

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
----------------------------	--------------------------------

STANDARDS TYPE	NEC/CEC
-----------------------	---------

NEC HAZARDOUS RATING	Class I, Division 1 Class II, Division 1 Class III
-----------------------------	--

NEMA RATING	3 3R
--------------------	---------

Product specifications

CONFIGURATION	Two-wire, three-pole
----------------------	----------------------

AMPERAGE RATING	20A
------------------------	-----

VOLTAGE RATING	125 Vac
-----------------------	---------

MATERIAL	Copper-free aluminum
-----------------	----------------------

Resources

BROCHURES	PowerGard Explosionproof NEMA Locking Receptacles brochure
CATALOGS	PowerGard Explosionproof NEMA Locking Receptacles catalog page
	PowerGard Explosionproof NEMA Locking Receptacles Canadian certification (Receptacles with Plugs Interlocked with Switches)
	PowerGard Explosionproof NEMA Locking Receptacles Canadian certification (Receptacles with Plugs)
CERTIFICATION REPORTS	PowerGard Explosionproof NEMA Locking Receptacles UL certification (PowerGard Receptacles and Back Boxes Classified for use with Crouse-Hinds ENP Plugs)
	PowerGard Explosionproof NEMA Locking Receptacles UL certification (PowerGard Receptacles and Back Boxes Classified for use with Appleton ECP Plugs and EFS Receptacles)
INSTALLATION INSTRUCTIONS	IF 1663 - PowerGard Receptacles
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CFSR-2023

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

