



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHB120 CHB Bolt-In Sftybrkr Aic *Eaton Corp*

| | |
|------------------|---|
| Catalog Number | CHB120 |
| Manufacturer | Eaton Corp |
| Description | Eaton CH Thermal Magnetic Circuit Breaker, Ground Fault Circuit Breaker, 5 Ma Ground Fault, 20 A, 10 Kaic, Single-Pole, 120/240 V, #14-8 Awg, CHB, CH Loadcenters |
| Weight per unit | 0.2800 (lbs/each) |
| Product Category | 1 Pole Standard Trip Bolt-On |

Features

| | |
|------------------|-----------------------------------|
| dimensions | 8.3000 IN X 4.5000 IN X 4.4000 IN |
| interrupt rating | 10 kAIC |
| Poles | Single-pole |
| Voltage Rating | 120/240 V |

Descriptions

| | |
|------------------------|---|
| Description | CHB BOLT-IN SFTYBRKR AIC |
| extra long description | ETN CHB120 CHB BOLT-IN SFTYBRKR AIC |
| Features | Eaton's residential CH circuit breakers provide premium overload protection. The Type CH circuit breakers trip to the OFF position, eliminating nuisance callbacks. The CHF family also includes a trip flag to differentiate between a trip and the breaker being turned off. The thermal-magnetic trip curve avoids nuisance tripping on mild overloads while reacting almost instantaneously to severe short-circuit conditions. Multiple breakers have an internal common trip connection to operate all poles simultaneous |
| Long Description | Eaton CH thermal magnetic circuit breaker,Ground fault circuit breaker,5 mA Ground fault,20 A,10 kAIC,Single-pole,120/240 V,#14-8 AWG,CHB,CH Loadcenters |
| Product Type | CHB Bolt-In Sftybrkr Aic |
| Special Features | 5 mA Ground fault |

Manufacturer Information

| | |
|---------------------------|---------------------|
| Brand | EATON CUTLER-HAMMER |
| GTIN | 00782113112350 |
| Manufacturers Part Number | CHB120 |
| UPC | 782113112350 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | PANELBOARD BRANCH BREAKERS |
| Type | Thermal magnetic circuit breakers |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.28 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | OtherDatacenters - IT Space: CI and Hyper ConvergedGeneration - Renewable Energy - Alternative EnergyGeneration - Conventional Energy - Conventional EnergyMarine Vessels and Equipment - Marine Vessels and Equipment - OtherResidential Bldgs & Facilities - Residential Bldgs & Facilities - Other |
| standard | UL 489,Contact Manufacturer |