



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHF120 Type CHF BRKR 20A/1P 120/240V 10 Kaic *Eaton Corp*

Catalog Number	CHF120
Manufacturer	Eaton Corp
Description	Eaton CH Thermal Magnetic Circuit Breaker, Type CHF 3/4-Inch Standard Circuit Breaker, 20 A, 10 Kaic, Single-Pole, 120/240V, CHF, Trip Flag, Common Breaker Trip, (1) #14-8 Awg, (2) #14-10 Awg Cu/Al, CHF, Type CH Loadcenters
Weight per unit	0.2800 (lbs/each)
Product Category	1 Pole Standard Trip Plug-In

Features

amps	20
dimensions	3.0000 IN X 0.7500 IN X 3.0000 IN
interrupt rating	10 kAIC
pole #	Single
Poles	1
Trip Type	Trip flag
Voltage Rating	120/240 V

Descriptions

extra long description	ETN CHF120 CHF BREAKER 20A / 1P 120
Features	Eaton's residential CH circuit breakers provide premium overload protection. The Type CH circuit breakers trip to the OFF position, eliminating nuisance callbacks. The CHF family also includes a trip flag to differentiate between a trip and the breaker being turned off. The thermal-magnetic trip curve avoids nuisance tripping on mild overloads while reacting almost instantaneously to severe short-circuit conditions. Multiple breakers have an internal common trip connection to operate all poles simultaneous
Long Description	Eaton CH Thermal magnetic circuit breaker, Type CHF 3/4-Inch standard circuit breaker, 20 A, 10 kAIC, Single-pole, 120/240V, CHF, Trip flag, common breaker trip, (1) #14-8 AWG, (2) #14-10 AWG Cu/Al, CHF, Type CH Loadcenters
Product Type	CHF Breaker 20A / 1P 120/240V 10 Kaic

Manufacturer Information

Brand	Eaton
GTIN	00786685361840
Manufacturers Part Number	CHF120
UPC	786685361840



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
Type	Thermal magnetic circuit breakers

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	0.28

Uses, Certifications, and Standards

Application	Datacenters - IT Space: CI and Hyper Converged Renewable Energy - Alternative Energy Generation - Conventional Energy Marine Vessels and Equipment - Marine Vessels and Equipment - Other
standard	UL 489, HACR Rated