



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHF140 Type CHF BRKR 40A/1P 120/240V 10kaic Eaton Corp

Catalog Number	CHF140
Manufacturer	Eaton Corp
Description	Eaton CH Thermal Magnetic Circuit Breaker, Type CHF 3/4-Inch Standard Circuit Breaker, 40 A, 10 Kaic, Single-Pole, 120/240V, CHF, Trip Flag, Common Breaker Trip, #14-2 Awg Cu/Al, CHF, Type CH Loadcenters
Weight per unit	0.2000 (lbs/each)
Product Category	1 Pole Standard Trip Plug-In

Features

dimensions	3.0000 IN X 0.7500 IN X 3.0000 IN
interrupt rating	10
Poles	1
Voltage Rating	120/240 V

Descriptions

Description	TYPE CHF BRKR 40A/1P 120/240V 10KAIC
extra long description	ETN CHF140 CHF BREAKER, 40A / 1P 12
Features	Eaton's residential CH circuit breakers provide premium overload protection. The Type CH circuit breakers trip to the OFF position, eliminating nuisance callbacks. The CHF family also includes a trip flag to differentiate between a trip and the breaker being turned off. The thermal-magnetic trip curve avoids nuisance tripping on mild overloads while reacting almost instantaneously to severe short-circuit conditions. Multiple breakers have an internal common trip connection to operate all poles simultaneous
Long Description	Eaton CH thermal magnetic circuit breaker, Type CHF 3/4-Inch standard circuit breaker, 40 A, 10 kAIC, Single-pole, 120/240V, CHF, Trip flag, common breaker trip, #14-2 AWG Cu/Al, CHF, Type CH Loadcenters
Product Type	CHF Breaker, 40A / 1P 120/240V 10kaic

Manufacturer Information

Brand	Eaton
GTIN	00786685532134
Manufacturers Part Number	CHF140
UPC	786685532134

Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
Type	Thermal magnetic circuit breakers



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	25
Weight Per each	0.2

Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative Energy Marine Vessels and Equipment - Marine Vessels and Equipment - OtherOtherGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper Converged
standard	UL 489,HACR Rated