



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHF140 Type CHF BRKR 40A/1P 120/240V 10kaic *Eaton Corp*

Catalog Number	CHF140
Manufacturer	Eaton Corp
Description	Eaton CH Thermal Magnetic Circuit Breaker, Type CHF 3/4-Inch Standard Circuit Breaker, 40 A, 10 Kaic, Single-Pole, 120/240V, CHF, Trip Flag, Common Breaker Trip, #14-2 Awg Cu/Al, CHF, Type CH Loadcenters
Weight per unit	0.2000 (lbs/each)
Product Category	1 Pole Standard Trip Plug-In

Features

amperage rating	40 A
dimensions	3.0000 IN X 0.7500 IN X 3.0000 IN
interrupt rating	10 kAIC
Poles	Single-pole
Trip Type	Trip flag
Voltage Rating	120/240 V

Descriptions

Description	TYPE CHF BRKR 40A/1P 120/240V 10KAIC
extra long description	ETN CHF140 CHF BREAKER, 40A / 1P 12
Features	Eaton's residential CH circuit breakers provide premium overload protection. The Type CH circuit breakers trip to the OFF position, eliminating nuisance callbacks. The CHF family also includes a trip flag to differentiate between a trip and the breaker being turned off. The thermal-magnetic trip curve avoids nuisance tripping on mild overloads while reacting almost instantaneously to severe short-circuit conditions. Multiple breakers have an internal common trip connection to operate all poles simultaneous
Long Description	Eaton CH thermal magnetic circuit breaker, Type CHF 3/4-Inch standard circuit breaker, 40 A, 10 kAIC, Single-pole, 120/240V, CHF, Trip flag, common breaker trip, #14-2 AWG Cu/Al, CHF, Type CH Loadcenters
Product Type	CHF Breaker, 40A / 1P 120/240V 10kaic

Manufacturer Information

Brand	Eaton
GTIN	00786685532134
Manufacturers Part Number	CHF140
UPC	786685532134



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Package	25
Weight Per each	0.2

Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative EnergyMarine Vessels and Equipment - Marine Vessels and Equipment - OtherOtherGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper Converged
standard	UL 489,HACR Rated