



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHP42B225X7 CH Pon Loadctr 225A Main BRKR 42 Space

Eaton Corp

Catalog Number	CHP42B225X7
Manufacturer	Eaton Corp
Description	Eaton CH Main Breaker Loadcenters, Pon, Main Breaker, 225 A, X7, Copper, X7, Nema 1, Metallic, 25 Kaic, CSR, 84, 42, Three-Wire, Single-Phase, #2 Awg-300 Kcmil, 120/240 V
Weight per unit	23.1 (lbs/each)
Product Category	Single Phase Main Breaker Load

Features

amperage rating	225
Cover Type	X7
interrupt rating	25
media	Yes
number of spaces	42
Phase	1
Voltage Rating	120/240 V

Dimensions and Weight

Depth	37
Height	3.88
Size	X7
Width	14.31

Descriptions

Description	CH PON LOADCNTR 225A MAIN BRKR 42 SPACE
extra long description	ETN CHP42B225X7 CH PON LC, 225A, MB
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH main breaker loadcenters,PON,Main breaker,225 A,X7,Copper,X7,NEMA 1,Metallic,25 kAIC,CSR,84,42,Three-wire,Single-phase,#2 AWG-300 kcmil,120/240 V
Product Type	CH Pon LC, 225A, MB, 42SP
Special Features	PON



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Eaton
GTIN	00786679189658
Manufacturers Part Number	CHP42B225X7
UPC	786679189658

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
Type	Main breaker loadcenter

Packaging

Carton	1
Weight Per each	23.1

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & EOEM - Electrical Assemblies, Panels and EOEMs
standard	UL 67,UL 50