

Eaton CHP24L225X5

Catalog Number: CHP24L225X5

Eaton CH main lug loadcenters,PON,CH,225A,X5,Copper,!,NEMA 1 indoor,Steel,25 kAIC,48,24,3,Single-phase,120/240 V,#4 AWG-300 kcmil



General specifications

Product Name	Catalog Number
Eaton CH main lug loadcenter	CHP24L225X5
UPC	Product Length/Depth
786689054281	29 in
Product Height	Product Width
4 in	14.3 in
Product Weight	Certifications
15.4 lb	UL 67

Catalog Notes
Purchase Size X5 Cover Separately

defaultTaxonomyAttributeLabel

Special features

PON

Type

CH

Amperage Rating

225 A

Bus material

Copper

Number of circuits

48

Number of spaces

24

Phase

Single-phase

Voltage rating

120/240 V

Box size

X5

Enclosure

NEMA 1

Enclosure material

Steel

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP24L225X5](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton CHP24L225X5

Catalog Number: CHP24L225X5

Eaton CH main lug loadcenters,PON,CH,225A,X5,Copper,!,NEMA 1 indoor,Steel,25 kAIC,48,24,3,Single-phase,120/240 V,#4 AWG-300 kcmil



General specifications

Product Name	Catalog Number
Eaton CH main lug loadcenter	CHP24L225X5
UPC	Product Length/Depth
786689054281	29 in
Product Height	Product Width
4 in	14.3 in
Product Weight	Certifications
15.4 lb	UL 67

Catalog Notes

Purchase Size X5 Cover Separately

defaultTaxonomyAttributeLabel

Special features

PON

Type

CH

Amperage Rating

225 A

Bus material

Copper

Number of circuits

48

Number of spaces

24

Phase

Single-phase

Voltage rating

120/240 V

Box size

X5

Enclosure

NEMA 1

Enclosure material

Steel

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP24L225X5](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)