



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHR8N8NSU Pop, Ringless, (2) 5-20R2GFI Receptacles, BTM Feed *Eaton Corp*

Catalog Number	CHR8N8NSU
Manufacturer	Eaton Corp
Description	Eaton Pedestal Mount Metered, Pos 1: GND Fault, Pos 2: Non-GND Fault, Pos 3: None, Bottom, Surface, Circuits: 4, Weather-Resist Center and Left Receptacle, Center: Nema 5-20R2GFI WR, Left: Nema 5-20R2GFI WR, Right: None, Ringless
Weight per unit	30.0 (lbs/each)
Product Category	Metered Power Outlet Pedestals

Features

dimensions	7.2500 IN X 10.0000 IN X 31.0000 IN
Mounting Type	Surface

Dimensions and Weight

Height	31.0000
Length	7.2500
Width	10.0000

Descriptions

Description	POP, RINGLESS, (2) 5-20R2GFI RECEPTACLES, BTM FEED
extra long description	ETN CHR8N8NSU POP RGLS (2) 5-20R2G
Features	Eaton's temporary power panels provide safe, reliable power for RV and construction sites. Durable, long-lasting units are available as metered (ring or ringless) or unmetered and can be mounted at the surface, on a pedestal, or in a back-to-back configuration.
Long Description	Eaton pedestal mount metered, Pos 1: Gnd fault, Pos 2: Non-gnd fault, Pos 3: None, Bottom, Surface, Circuits: 4, Weather-resist center and left receptacle, Center: NEMA 5-20R2GFI WR, Left: NEMA 5-20R2GFI WR, Right: None, Ringless
Product Type	Pop RGLS (2) 5-20R2GFI Recps BTM Feed
Special Features	Water resistant left/center receptacle

Manufacturer Information

Brand	Eaton
GTIN	00786685404202
Manufacturers Part Number	CHR8N8NSU
UPC	786685404202

Taxonomies, Classifications, and Categories

Category Description	RV Power Pedestals
Type	Pedestal mount metered



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
--------	---

Weight Per each	30
-----------------	----

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
-------------	--

Mounting	SURFACE
----------	---------

standard	UL Listed file E163588,UL 231
----------	-------------------------------