



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHR8N8NSU Pop, Ringless, (2) 5-20R2GFI Receptacles, BTM Feed *Eaton Corp*

Catalog Number	CHR8N8NSU
Manufacturer	Eaton Corp
Description	Eaton Pedestal Mount Metered, Pos 1: GND Fault, Pos 2: Non-GND Fault, Pos 3: None, Bottom, Surface, Circuits: 4, Weather-Resist Center and Left Receptacle, Center: Nema 5-20R2GFI WR, Left: Nema 5-20R2GFI WR, Right: None, Ringless
Weight per unit	30.0 (lbs/each)
Product Category	Metered Power Outlet Pedestals

Features

dimensions	7.2500 IN X 10.0000 IN X 31.0000 IN
------------	-------------------------------------

Descriptions

Description	POP, RINGLESS, (2) 5-20R2GFI RECEPTACLES, BTM FEED
extra long description	ETN CHR8N8NSU POP RNLGS (2) 5-20R2G
Features	Eaton's temporary power panels provide safe, reliable power for RV and construction sites. Durable, long-lasting units are available as metered (ring or ringless) or unmetered and can be mounted at the surface, on a pedestal, or in a back-to-back configuration.
Long Description	Eaton pedestal mount metered, Pos 1: Gnd fault, Pos 2: Non-gnd fault, Pos 3: None, Bottom, Surface, Circuits: 4, Weather-resist center and left receptacle, Center: NEMA 5-20R2GFI WR, Left: NEMA 5-20R2GFI WR, Right: None, Ringless
Product Type	Pop RNLGS (2) 5-20R2GFI Recps BTM Feed
Special Features	Water resistant left/center receptacle

Manufacturer Information

Brand	Eaton
GTIN	00786685404202
Manufacturers Part Number	CHR8N8NSU
UPC	786685404202

Taxonomies, Classifications, and Categories

Category Description	RV Power Pedestals
Type	Pedestal mount metered

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	30



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels
and OEMs

Mounting

SURFACE

standard

UL Listed file E163588,UL 231