



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **CHR9N9NS Pop Ringless 2 5-20R2GFI Receptacles,** *Eaton Corp*

Catalog Number	CHR9N9NS
Manufacturer	Eaton Corp
Description	Eaton Pedestal Mount Metered, Pos 1: Non-GND Fault, Pos 2: Non-GND Fault, Pos 3: None, Weather and Tamper Resist Center and Left Receptacle, Center: Nema 5-20R2GFI WR TR, Left: Nema 5-20R2GFI WR TR, Right: None, Ringless
Weight per unit	30.0 (lbs/each)
Product Category	Metered Power Outlet Pedestals

### **Features**

dimensions	30.5000 IN X 10.0000 IN X 7.0000 IN
Mounting Type	Surface

### **Dimensions and Weight**

Height	7.0000
Length	30.5000
Width	10.0000

### **Descriptions**

Description	POP RINGLESS 2 5-20R2GFI RECEPTACLES,
extra long description	ETN CHR9N9NS POP, RINGLESS, (2) 5-2
Features	Eaton's temporary power panels provide safe, reliable power for RV and construction sites. Durable, long-lasting units are available as metered (ring or ringless) or unmetered and can be mounted at the surface, on a pedestal, or in a back-to-back configuration.
Long Description	Eaton pedestal mount metered, Pos 1: Non-gnd fault, Pos 2: Non-gnd fault, Pos 3: None, Weather and tamper resist center and left receptacle, Center: NEMA 5-20R2GFI WR TR, Left: NEMA 5-20R2GFI WR TR, Right: None, Ringless
Product Type	Pop, Ringless, (2) 5-20R2GFI Recp
Special Features	Water and tamper resistant left/center receptacle

### **Manufacturer Information**

Brand	Eaton
GTIN	00786685409542
Manufacturers Part Number	CHR9N9NS
UPC	786685409542

### **Taxonomies, Classifications, and Categories**

Category Description	RV Power Pedestals
Type	Pedestal mount metered



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	30

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting	SURFACE
standard	UL 231,UL Listed file E163588