



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

17 Lou Stroup Drive  
78801-0000, TX Uvalde  
Phone: 830-278-1938  
Fax: 830-278-1395



## CHR9N9NSU Pop Ringless 2 5-20R2GFI Receptacles BTM Feed

Eaton Corp

Catalog Number	CHR9N9NSU
Manufacturer	Eaton Corp
Description	Eaton Pedestal Mount Metered, Pos 1: Non-GND Fault, Pos 2: Non-GND Fault, Pos 3: None, Circuits: 4, Weather and Tamper Resist Center and Left Receptacle, Center: Nema 5-20R2GFI WR TR, Left: Nema 5-20R2GFI WR TR, Right: None, Ringless
Weight per unit	30.0 (lbs/each)
Product Category	Metered Power Outlet Pedestals

### Features

Mounting Type	Surface
---------------	---------

### Dimensions and Weight

Height	7
Length	30.5
Width	10

### Descriptions

Description	POP RINGLESS 2 5-20R2GFI RECEPTACLES BTM FEED
extra long description	ETN CHR9N9NSU POP, RINGLESS, (2) 5-
Features	Eaton's temporary power panels provide safe, reliable power for RV and construction sites. Durable, long-lasting units are available as metered (ring or ringless) or unmetered and can be mounted at the surface, on a pedestal, or in a back-to-back configuration.
Long Description	Eaton pedestal mount metered, Pos 1: Non-gnd fault, Pos 2: Non-gnd fault, Pos 3: None, Circuits: 4, Weather and tamper resist center and left receptacle, Center: NEMA 5-20R2GFI WR TR, Left: NEMA 5-20R2GFI WR TR, Right: None, Ringless
Product Type	Pop, Ringless, (2) 5-20R2GFI, BTM Feed
Special Features	Water and tamper resistant left/center receptacle

### Manufacturer Information

Brand	Eaton Corp
GTIN	00786685404219
Manufacturers Part Number	CHR9N9NSU
UPC	786685404219

### Taxonomies, Classifications, and Categories

Category Description	RV Power Pedestals
Type	Pedestal mount metered



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

17 Lou Stroup Drive  
78801-0000, TX Uvalde  
Phone: 830-278-1938  
Fax: 830-278-1395

## Packaging

Carton	1
Weight Per each	30

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
standard	UL 231,UL Listed file E163588