



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHR1G7N7NSU Bottom Fed Metered Ringless Surface Pop W/(1) 14- Eaton Corp

Catalog Number	CHR1G7N7NSU
Manufacturer	Eaton Corp
Description	Eaton Pedestal Mount Metered, Pos 1: GND Fault, Pos 2: Non-GND Fault, Pos 3: Non-GND Fault, Bottom, Surface, Circuits: 4, Center: Nema 5-20R2GFI, Left: Nema 14-50R, Right: Nema 5-20R2GFI, Ringless
Weight per unit	24.0 (lbs/each)
Product Category	Metered Power Outlet Panels

Features

dimensions	31.0000 IN X 10.0000 IN X 8.0000 IN
------------	-------------------------------------

Dimensions and Weight

Depth	31.0000
Height	8.0000
Width	10.0000

Descriptions

Description	BOTTOM FED METERED RINGLESS SURFACE POP W/(1) 14-
extra long description	ETN CHR1G7N7NSU BTM Fed MTRD RL Sur
Features	Eaton's temporary power panels provide safe, reliable power for RV and construction sites. Durable, long-lasting units are available as metered (ring or ringless) or unmetered and can be mounted at the surface, on a pedestal, or in a back-to-back configuration.
Long Description	Eaton pedestal mount metered, Pos 1: Gnd fault, Pos 2: Non-gnd fault, Pos 3: Non-gnd fault, Bottom, Surface, Circuits: 4, Center: NEMA 5-20R2GFI, Left: NEMA 14-50R, Right: NEMA 5-20R2GFI, Ringless
Product Type	BTM Fed MTRD RL Surface Pop(1)1450R(2)5

Manufacturer Information

Brand	Viton(R)
GTIN	00782116153367
Manufacturers Part Number	CHR1G7N7NSU
UPC	782116153367

Taxonomies, Classifications, and Categories

Category Description	RV Power Pedestals
Type	Pedestal mount metered

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	24

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting	SURFACE
standard	UL 231,UL Listed file E163588