



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHR3G9N9NS Metered-Ringless Pop Surface

Eaton Corp

Catalog Number	CHR3G9N9NS
Manufacturer	Eaton Corp
Description	Eaton Pedestal Mount Metered, Pos 1: GND Fault, Pos 2: Non-GND Fault, Pos 3: Non-GND Fault, Weather and Tamper Resist Center and Right Receptacle, Center: Nema 5-20R2GFI WR TR, Left: Nema 14-30R, Right: Nema 5-20R2GFI WR TR, Ringless
Weight per unit	30.0 (lbs/each)
Product Category	Metered Power Outlet Pedestals

Features

dimensions	31.0000 IN X 10.0000 IN X 7.5000 IN
------------	-------------------------------------

Dimensions and Weight

Depth	31.0000
Height	7.5000
Width	10.0000

Descriptions

Description	METERED-RINGLESS POP SURFACE
extra long description	ETN CHR3G9N9NS METERED-RINGLESS POP
Features	Eaton's temporary power panels provide safe, reliable power for RV and construction sites. Durable, long-lasting units are available as metered (ring or ringless) or unmetered and can be mounted at the surface, on a pedestal, or in a back-to-back configuration.
Long Description	Eaton pedestal mount metered, Pos 1: Gnd fault, Pos 2: Non-gnd fault, Pos 3: Non-gnd fault, Weather and tamper resist center and right receptacle, Center: NEMA 5-20R2GFI WR TR, Left: NEMA 14-30R, Right: NEMA 5-20R2GFI WR TR, Ringless
Product Type	Metered-Ringless Pop, Surface
Special Features	Water and tamper resistant center/right receptacle

Manufacturer Information

Brand	Eaton
GTIN	00786685552743
Manufacturers Part Number	CHR3G9N9NS
UPC	786685552743

Taxonomies, Classifications, and Categories

Category Description	RV Power Pedestals
Type	Pedestal mount metered



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	30

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting	SURFACE
standard	UL Listed file E163588,UL 231