



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHR9N9NKGS Pop TF RL 20/20/20 *Eaton Corp*

Catalog Number	CHR9N9NKGS
Manufacturer	Eaton Corp
Description	Eaton Pedestal Mount Metered, Top, Surface, Circuits: 4, Weather-Resist and Tamper Resist Center and Left Receptacle, Weather Resist Right Receptacle, Center: Nema 5-20R2GFI WR TR, Left: Nema 5-20R2GFI WR TR, Right: Nema 6-20R2 WR, Ringless
Weight per unit	30.0 (lbs/each)
Product Category	Metered Power Outlet Pedestals

Features

dimensions	30.0000 IN X 9.0000 IN X 6.5000 IN
Mounting Type	Surface

Dimensions and Weight

Height	6.5000
Length	30.0000
Width	9.0000

Descriptions

Description	POP TF RL 20/20/20
extra long description	ETN CHR9N9NKGS POP, TF, RL, 20/20/2
Features	Eaton's temporary power panels provide safe, reliable power for RV and construction sites. Durable, long-lasting units are available as metered (ring or ringless) or unmetered and can be mounted at the surface, on a pedestal, or in a back-to-back configuration.
Long Description	Eaton pedestal mount metered, Top, Surface, Circuits: 4, Weather-resist and tamper resist center and left receptacle, weather resist right receptacle, Center: NEMA 5-20R2GFI WR TR, Left: NEMA 5-20R2GFI WR TR, Right: NEMA 6-20R2 WR, Ringless
Product Type	Pop, TF, RL, 20/20/20

Manufacturer Information

Brand	Eaton Corp
GTIN	00786680193606
Manufacturers Part Number	CHR9N9NKGS
UPC	786680193606

Taxonomies, Classifications, and Categories

Category Description	RV Power Pedestals
Type	Pedestal mount metered



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	30

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting	SURFACE
standard	UL 231,UL Listed file E163588