

Eaton CHU3S

Catalog Number: CHU3S

Eaton pedestal mount unmetered, Unmetered, 30A, None, None, None, None, None, Top, Surface, Circuits: 4, NEMA 14-30R, None, None, 4, 0, 0, 125/250V, None, None

General specifications



Product Name

Eaton pedestal mount unmetered

Catalog Number

CHU3S

UPC

782116128198

Product Length/Depth

13.6 in

Product Height

39.9 in

Product Width

9.5 in

Product Weight

5 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed file E163588

UL 231

Physical Attributes

Circuit breaker position 1

None

Circuit breaker position 2

None

Circuit breaker position 3

None

Feed type

Top

Mounting

Surface

Number of circuits

4

Receptacle center

None

Receptacle left

NEMA 14-30R

Receptacle right

None

Type

Unmetered

Resources

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CHU3S](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton CHU3S

Catalog Number: CHU3S

Eaton pedestal mount unmetered, Unmetered, 30A, None, None, None, None, None, Top, Surface, Circuits: 4, NEMA 14-30R, None, None, 4, 0, 0, 125/250V, None, None

General specifications



Product Name

Eaton pedestal mount unmetered

Catalog Number

CHU3S

UPC

782116128198

Product Length/Depth

13.6 in

Product Height

39.9 in

Product Width

9.5 in

Product Weight

5 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed file E163588

UL 231

Physical Attributes

Circuit breaker position 1

None

Circuit breaker position 2

None

Circuit breaker position 3

None

Feed type

Top

Mounting

Surface

Number of circuits

4

Receptacle center

None

Receptacle left

NEMA 14-30R

Receptacle right

None

Type

Unmetered

Resources

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CHU3S](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia