



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CHU9N9NS Pop Ringless 2 5-20R2GFI Receptacles Surface

*Eaton Corp*

Catalog Number	CHU9N9NS
Manufacturer	Eaton Corp
Description	Eaton Pedestal Mount Unmetered, Water and Tamper Resistant Left/Center Receptacle, Unmetered, 20A, 20A, None, Non-GF, Non-Ground Fault, None, Top, Surface, Circuits: 4, Nema 5-20R2GFI(3), Nema 5-20R2GFI(3), None, 3, 3, 0, 125V, 125V, None
Weight per unit	15.0 (lbs/each)
Product Category	20191018094527

### Features

dimensions	4.3000 IN X 9.5000 IN X 17.1000 IN
Mounting Type	Surface

### Dimensions and Weight

Height	17.1000
Length	4.3000
Width	9.5000

### Descriptions

Description	POP RINGLESS 2 5-20R2GFI RECEPTACLES SURFACE
extra long description	ETN CHU9N9NS POP,RINGLESS,(2) 5-20R
Features	Eaton's temporary power panels provide safe, reliable power for RV and construction sites. Durable, long-lasting units are available as metered (ring or ringless) or unmetered and can be mounted at the surface, on a pedestal, or in a back-to-back configuration.
Long Description	Eaton pedestal mount unmetered, Water and tamper resistant left/center receptacle, Unmetered, 20A, 20A, None, Non-GF, Non-ground fault, None, Top, Surface, Circuits: 4, NEMA 5-20R2GFI(3), NEMA 5-20R2GFI(3), None, 3, 3, 0, 125V, 125V, None
Product Type	Pop, Ringless, (2) 5-20R2GFI Recept, Surf
Special Features	Water and tamper resistant left/center receptacle

### Manufacturer Information

Brand	Eaton Corp
GTIN	00786685404233
Manufacturers Part Number	CHU9N9NS
UPC	786685404233



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	RV Power Pedestals
Type	Pedestal mount unmetered

## Packaging

Carton	1
Weight Per each	15

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting standard	SURFACE UL 231,UL Listed file E163588