

CI-200 Passive Infrared Sensor

360° coverage

User adjustable time delay and sensitivity

ASIC enhances reliability and helps eliminate false triggers



Isolated relay for use with HVAC or other control systems (CI-200)

Built-in light level sensor (CI-200)


Specifications

- Time delay 15 sec to 30 min
- Built-in light level sensor 4 to 190 fc (43 to 2,045 lux) (CI-200)
- SPDT isolated relay (CI-200)
- Units per power pack: CI-200 up to 5 (B), up to 7 (BZ); CI-205 up to 10 (B), up to 13 (BZ)
- 3.3" diameter x 2.2" total depth (83.8mm x 55.9mm) Extends approx .36" from ceiling
- UL and CUL listed, 5 year warranty


Applications

- Open or partitioned office spaces
- Conference rooms
- Computer rooms
- Classrooms

Wiring & Controls



Coverage Patterns



Order Information

CATALOG #	VOLTAGE	CURRENT	COVERAGE
CI-200	24 VDC	20 mA	up to 1200 ft ² (111.5 m ²)
CI-200-1	24 VDC	20 mA	up to 500 ft ² (46.5 m ²)
CI-205	24 VDC	11 mA	up to 1200 ft ² (111.5 m ²)
CI-205-1	24 VDC	11 mA	up to 500 ft ² (46.5 m ²)

All units are white and use Watt Stopper power packs.

Product Line Summary

	WS-200	120/277 VAC; 60 Hz	Automatic wall switch	Passive infrared
	WA-200 WA-300	120/277 230/277 VAC, 50/60 Hz 120/277 230/277 VAC, 50/60 Hz	Automatic wall switch -with dual relays	Passive infrared Passive infrared
	WI-200 WI-300	120/277 VAC; 60 Hz 120/277 VAC; 60 Hz	Automatic wall switch -with dual relays	Passive infrared Passive infrared
	WN-100-120 WN-100-277	120 VAC, 60 Hz 277 VAC, 60 Hz	Motion sensor nightlight switch Motion sensor nightlight switch	Passive infrared Passive infrared
	WD Series	120 or 277 VAC; 60 Hz	Dimmable wall switch	Passive infrared
	CN-100 CW-100	120 VAC, 60 Hz 120 VAC, 60 Hz	Residential vacancy sensor Residential vacancy sensor	Passive infrared Passive infrared
	WPIR	24 VDC	Ceiling mount sensor	Passive infrared
	CX Series	24 VDC	Ceiling/wall mount sensor	Passive infrared
	CI-200 Series	24 VDC	Ceiling mount sensor	Passive infrared
	CI-300 Series CI-355 Series	24 VDC 120/230/277/347 VAC; 50/60 Hz	Ceiling mount sensor Ceiling mount sensor	Passive infrared Passive infrared
	CI-12/24	12/24 VDC	Sensor for HVAC, BAS	Passive infrared
	CB-100	24 VDC	Low temperature sensor	Passive infrared
	W Series	24 VDC	Ceiling mount sensor	Ultrasonic
	WT Series	24 VDC	Ceiling mount sensor	Ultrasonic
	UT-300 Series UT-355 Series	24 VDC 120/230/277/347 VAC; 50/60 Hz	Ceiling mount sensor Ceiling mount sensor	Ultrasonic Ultrasonic
	DT-200 Series	24 VDC	Ceiling/wall mount sensor	Dual technology
	DT-300 Series DT-355 Series	24 VDC 120/230/277/347 VAC; 50/60 Hz	Ceiling mount sensor Ceiling mount sensor	Dual technology Dual technology

